



# FXCS Series Maintained Contact 2-Position Keyed Selector Switch Cover With Device - Factory Sealed 2NO/2NC Contact

By Killark  
Catalog # [FXCS-0K2A5](#)

FXCS Series - Aluminum Maintained Contact 2-Position Keyed Selector Switch Cover With Device - Factory Sealed 2NO/2NC Contact.



\*Representative Image

## Features

- Eliminates external sealing requirements.
- Lower installation cost.
- NEMA 3 weatherproof.
- Color coded wiring with more wiring space for easier field installation.
- Stainless steel captive screws for cover assembly.
- Lockout accessory available must be factory installed.
- Ground boss for grounding in the splicebox.
- Device bodies and covers are copper-free cast aluminum alloy.
- Push button, selector switches and pilot light bodies are copper-free aluminum.
- Operating shaft in both push buttons and selector switches are stainless steel.

## Application

SEAL-X Series is used to prevent the igniting of external hazardous atmospheres by the enclosed arcing devices in such areas as: hazardous locations due to the presence of flammable gases or vapors, combustible dusts or easily ignitable fibers or flyings

## General

Action	Maintained
Actuator	2 Position Key Selector Switch
Back Box Type	FXB
Color	<ul style="list-style-type: none"><li>• Black</li><li>• Noir</li></ul>
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Number Of Poles	1
Series	FXCS
Type	<ul style="list-style-type: none"><li>• Aluminum Factory Sealed Cover With 2-Position Key Selector Switch</li><li>• Aluminum Factory Sealed Cover With 2-Position Key Selector Switch</li></ul>
UPC	783936200620

## Dimensions

Dimensions	6.5 in x 6.125 in x 4.75 in
Gross Weight with Packaging	3.14
Height	4.75 in
Length	6.5 in
Weight	3.14 lb
Width	6.125 in

## Electrical Ratings

Amperage Rating	10 A
Frequency Rating	50/60 Hz

## Certifications and Compliance

CSA File Number	LR11714, LR11712
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
Nema Rating	3
UL File Number	E53360, E12379

## Logistics

Factory Sealed	Factory Sealed
----------------	----------------

## Product Assets

[Catalogs - Killark Catalog](#)  
[Certifications - FXB, FXCS, & FXS Series Control Stations UL Certification](#)  
[Certifications - FXCS Series Factory Sealed Control Stations CSA Certification](#)  
[Certifications - FXCS & XCS Series Auxiliary Devices UL Certification](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - FXCS IOM K0889 French](#)  
[Installation Manuals - FXCS IOM K0889](#)



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
KILL\_CA-FXCS-OK2A5-SPEC-EN | REV 1/2024