



**FXCS-OB4 - FXCS Series, AL
Momentary Contact Double Push
Button Cover w/ Device, Green
Button w/ 'Start', Red Button w/
'Stop', 1NO/1NC Contact Rating**

By Killark
Catalog # [FXCS-OB4](#)



*Representative Image

FXCS Series - Aluminum Momentary Contact Double Push
Button Cover With Device - Factory Sealed - Green Button With
"Start" Nameplate - Red Button With "Stop" Nameplate -
1NO/1NC Contact Rating

Features

-
-
-
-
-
-
-
-
-
-

General

Action	Momentary
Actuator	Double Pushbutton
Back Box Type	FXB
Catalog Number	FXCS-OB4
Color	Green-Red
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Number Of Poles	2
Series	FXCS
UPC	783936200477

Dimensions

Dimensions	6.75 in x 6.25 in x 4.875 in
Gross Weight with Packaging	2.91
Height	4.875 in
Length	6.75 in
Weight	2.91 lb
Width	6.25 in

Electrical Ratings

Amperage Rating	10 A
Frequency Rating	50/60 Hz

Certifications And Compliance

CSA File Number	LR11714, LR11712
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
Nema Rating	3
UL File Number	E53360, E12379

Logistics

Factory Sealed	Factory Sealed
----------------	----------------

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - FXCS Series Factory Sealed Control Stations CSA Certification](#)
- [Certifications - FXCS & XCS Series Auxiliary Devices UL Certification](#)
- [Certifications - FXB, FXCS, & FXS Series Control Stations UL Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - FXCS IOM K0889](#)
- [Installation Manuals - FXCS IOM K0889 French](#)
- [Specifications - FXCS0B4 Specification Sheet English](#)
- [Specifications - FXCS-OB4 Specification Sheet French](#)
- [Specifications - FXCS Series Factory Sealed Cover Assemblies Specification Sheet](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
KILL_CA-FXCS0B4-SPEC-EN | REV 4/2025