



G Series Long Maintained Contact 2-Position Selector Switch Operator - "Off - On"/Blank Nameplate - 1NO/1NC Contact Rating

By Killark
Catalog # [GO5-2A3F N34](#)



*Representative Image

Killark GO SERIES Operators are a component use in conjunction with a Hazardous Location enclosure to provide control solutions in for; START/STOP Motor Functions, LED Pilot Light Indications and more. Utilized in Class 1 Division 1 & 2, Class 1 Zone 1 & 2 areas for indoor and outdoor use. UL Listed and CSA Certified.

Features

-
-
-
-

General

| | |
|---------------------|--|
| Action | Rotary |
| Actuator | 2 Position Selector Switch |
| Ambient Temp. Range | UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C |
| Catalog Number | GO5-2A3F N34 |
| Color | Black |
| EU RoHS Indicator | Contact Manufacturer |
| Number Of Poles | 1 |
| Series | GO |
| UPC | 783936997209 |

Dimensions

| | |
|-----------------------------|----------------------------|
| Dimensions | 6.5 in x 2.25 in x 1.75 in |
| Gross Weight with Packaging | 0.5 |
| Height | 1.75 in |
| Length | 6.5 in |
| Width | 2.25 in |

Electrical Ratings

| | |
|-----------------|--|
| Amperage Rating | 10 A |
| Contact Rating | 60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A INRUSH @ 480 VAC; 12A INRUSH @ 600 VAC; 0.55A INRUSH @ 125 VDC; 0.275A |

INRUSH @ 250 VDC; 6A
BREAKING @ 120 VAC; 3A
BREAKING @ 240 VAC; 1.5A
BREAKING @ 480 VAC; 1.2A
BREAKING @ 600 VAC; 0.55A
BREAKING @ 125 VDC; 0.275A
BREAKING @ 250 VDC; 10A
CARRYING @ 120 VAC; 10A
CARRYING @ 240 VAC; 10A
CARRYING @ 480 VAC; 10A
CARRYING @ 600 VAC; 2.5A
CARRYING @ 125 VDC; 2.5A
CARRYING @ 250 VDC.
50/60 Hz

Frequency Rating

Certifications And Compliance

| | |
|---------------------|---|
| CSA File Number | LR11714 |
| Hazardous Rating(s) | <ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups B, C, D• Class I, Zones 1 & 2, Groups IIB, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2 |
| Nema Rating | 3, 4, 4X |
| UL File Number | E12379 |

Product Assets

- [Certifications - GO Series Operators CSA Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - GO52A3FN34 Specification Sheet English](#)
- [Specifications - GO5-2A3F N34 Specification Sheet French](#)
- [Specifications - G Series Selector Switches Specification Sheet](#)