



# GZ Series Potentiometer, Multi Turn 10K Ohm Extra Long Length 57mm, 3/4 NPSM

By Killark  
Catalog # [GZL114-10K](#)



Potentiometer, Multi Turn 10K Ohm Extra Long Length 57mm, 3/4 NPSM.

\*Representative Image

## Features

- Operators are all aluminum except for certain movable parts which are stainless steel.
- All other parts such as screws are either stainless steel or plated steel.
- Threaded bodies are all 3/4"-14 NPSM thread and M22x1.5 on request.
- Control operators can be grouped into a single assembly thus reducing installation time and cost.

## General

|                   |   |
|-------------------|---|
| Action            | Rotary  |
| Color             | <ul style="list-style-type: none"><li>• Black</li><li>• Noir</li></ul>                  |
| EU RoHS Indicator | Contact Manufacturer  |
| Series            | GZ  |
| Type              | <ul style="list-style-type: none"><li>• Potentiometer</li><li>• Potentiometer</li></ul> |
| UPC               | 783936178943  |

## Dimensions

|            |                          |
|------------|--------------------------|
| Dimensions | 6.6 in x 1.8 in x 1.3 in |
| Height     | 1.3 in                   |
| Length     | 6.6 in                   |
| Weight     | 0.37 lb                  |
| Width      | 1.8 in                   |

## Electrical Ratings

|                  |          |
|------------------|----------|
| Frequency Rating | 50/60 Hz |
| Wattage          | 0.25 W   |

## Certifications and Compliance

|                     |  |
|---------------------|--|
| ATEX File Number    | SIRA 19ATEX 1171 U   |
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups B, C, D</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li><li>• Zones 1 &amp; 2</li><li>• Zones 21 &amp; 22</li><li>• II 2 G Ex db IIC/IIB+H2Gb</li><li>• II 2 D Ex tb IIIC Db</li></ul> |
| IECEX File Number   | IECEX SIR 19.0054 U  |
| Nema Rating         | Type 4X  |
| UL File Number      | E12379   |

## Product Assets

- [Certifications - GZ Series ATEX Certificate](#)
- [Certifications - GZ Series Attestation of Conformity](#)
- [Certifications - GZ Series UL Certificate](#)
- [Certifications - GZ Series IECEX Certificate](#)
- [Engineering Drawing - GZ Series Dimensional Drawings \(DWG\)](#)
- [Installation Manuals - GZ Series Potentiometers Installation Manual K1503](#)
- [Sales Drawings - GZ Series Dimensional Drawings \(PDF\)](#)
- [Video - GZ Operators](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
KILL\_CA-GZL114-10K-SPEC-EN | REV 1/2024