



KFL3030 - KFL-X 30000 LUMEN 120-277 VAC 50/60 Hz 3000K CCT 70 CRI

By Killark
Catalog # [KFL3030](#)

KFL-X 30000 LUMEN 120-277 VAC 50/60 Hz 3000K CCT 70 CRI

Features

-
-
-
-
-
-
-
-
-

General

Catalog Number	KFL3030
Color Temperature	5000 K
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lumen Range	25,001-50,000 lm
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Operating Temperature	-50°C to +40 °C
Optic Type	Glass Lens
Series	KFL-X
UPC	783936183220

Dimensions

Hub Size	3/4 NPT or M25
----------	----------------

Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	120-277 VAC
Wattage	280 W

Certifications And Compliance

ATEX File Number	Presafe 19 ATEX 32747X (ec)Presafe 19 ATEX 33512 (tb)
CSA File Number	80004509



Hazardous Rating(s)

- Class I, Division 2, Groups A,B,C,D
- Class II, Division 1 & 2, Groups E,F,G
- Class III, Divisions 1 & 2
- Zone 2
- Zone 21
- Ex ec op is IIC T5/T4 Gc
- Ex op is tb IIIC T95°C Db

IECEx File Number

QPS 19.0031X

IP Rating

IP66

Nema Rating

Type 4X

Product Assets

- [3D Models - KFL-X Series 3D Model](#)
- [3D Models - KFL-X Series With Dark Sky 3D Model](#)
- [3D Product View - KFL-X](#)
- [Brochures - KFL-X Brochure](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - KFLX Series UKCA UK Type Certification](#)
- [Certifications - KFLX Series Attestation of Conformity](#)
- [Certifications - KFLX Series IEx Certificate of Conformity](#)
- [Certifications - KFL-X Series IECEx Certificate of Conformity](#)
- [Certifications - KFLX Series UKCA Certification](#)
- [Certifications - KFL-X Series ATEX Certificate EU Type](#)
- [Certifications - KFL-X Series CSA Certificate](#)
- [Certifications - KFL-X Series ATEX Certificate](#)
- [Engineering Drawing - KFL-X Series With Dark Sky 2D Engineering Drawing](#)
- [Engineering Drawing - KFL-X Series 2D Engineering Drawing](#)
- [Installation Manuals - KFL-X Series IOM K1505](#)
- [Photometry - KFL3030 IES File](#)
- [Sales Drawings - KFL-X Series With Dark Sky Sales Drawing](#)
- [Sales Drawings - KFL-X Series Sales Drawing](#)
- [Specifications - KFL3030 Specification Sheet English](#)
- [Specifications - KFL-X Series Floodlights Specification Sheet](#)
- [Specifications - KFL3030 Specification Sheet French](#)
- [Video - KFL-X Product Video](#)
- [Video - KFL-X Product Video](#)



A Hubbell brand