



FXCS Series Spring Returned 2-Position Keyed Selector Switch Cover With Device - Factory Sealed 1NO/1NC Contact- Keyed Alike

By Killark
Catalog # FXCS-0K2L3F22A

FXCS Series - Aluminum Spring Returned 2-Position Keyed Selector Switch Cover With Device - Factory Sealed 1NO/1NC Contact- Keyed Alike.



*Representative Image

Features

- Eliminates external sealing requirements.
- Lower installation cost.
- NEMA 3 weatherproof.
- Color coded wiring with more wiring space for easier field installation.
- Stainless steel captive screws for cover assembly.
- Lockout accessory available must be factory installed.
- Ground boss for grounding in the splicebox.
- Device bodies and covers are copper-free cast aluminum alloy.
- Push button, selector switches and pilot light bodies are copper-free aluminum.
- Operating shaft in both push buttons and selector switches are stainless steel.

General

Action	Momentary
Actuator	2 Position Key Selector Switch
Application	
Back Box Type	FXB
Catalog Number	FXCS-0K2L3F22A
Color	Black
	Noir
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Number Of Poles	1
Series	FXCS
Type	
UPC	783936039343

Dimensions

Dimensions	6.63 in x 6 in x 4.38 in
Gross Weight with Packaging	3.5
Height	4.38 in
Length	6.63 in
Weight	3.5 lb
Width	6 in

Electrical Ratings

Amperage Rating	10 A
Frequency Rating	50/60 Hz

Certifications And Compliance

CSA File Number	LR11714, LR11712
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, D
	Class I, Zones 1 & 2, Groups IIB, IIA
	Class II, Divisions 1 & 2, Groups E, F, G
	Class III, Divisions 1 & 2
Nema Rating	3
UL File Number	E53360, E12379

Logistics

Carton Quantity	5
Factory Sealed	Factory Sealed

Product Assets

- [Certifications - FXCS & XCS Series Auxiliary Devices UL Certification](#)
- [Certifications - FXB, FXCS, & FXS Series Control Stations UL Certification](#)
- [Certifications - FXCS Series Factory Sealed Control Stations CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - FXCS IOM K0889 French](#)
- [Installation Manuals - FXCS IOM K0889](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-FXCS0K2L3F22A-SPEC-EN | REV 6/2024