



# FXS Series - Dead-End Ground Fault Interrupter Unit - Factory Sealed - Hub Size 1/2 Inch - 20A/120Vac/60Hz - 4-6 Milliamp Trip Setting

By Killark  
Catalog # [FXS-GFI-1020](#)

FXS Series - Aluminum Dead-End Ground Fault Interrupter Unit - Factory Sealed - Hub Size 1/2" - 20A/120Vac/60Hz - 4-6 Milliamp Trip Setting.



\*Representative Image

## Features

- Eliminates external sealing requirements.
- Lower installation cost.
- NEMA 3 weatherproof.
- Color coded wiring with more wiring space for easier field installation.
- Stainless steel captive screws for cover assembly.
- Lockout accessory available must be factory installed.
- Ground boss for grounding in the splicebox.
- Device bodies and covers are copper-free cast aluminum alloy.
- Push button, selector switches and pilot light bodies are copper-free aluminum.
- Operating shaft in both push buttons and selector switches are stainless steel.

## Application

FXS ground fault interrupters are designed to interrupt a circuit when a ground fault is detected on equipment which may be handled by personnel in hazardous locations.

## General

Action	Push buttons
Actuator	Ground Fault Interrupter
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Back Box Type	FXB
Color	<ul style="list-style-type: none"> <li>• Gray</li> <li>• Gris</li> </ul>
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Number Of Poles	2
Series	FXS-GFI
Type	<ul style="list-style-type: none"> <li>• Aluminum Factory Sealed Ground Fault Interrupter</li> <li>• Aluminum Factory Sealed Ground Fault Interrupter</li> </ul>
UPC	783936198361

## Dimensions

Depth	5-1/8
Gross Weight with Packaging	5

## Electrical Ratings

Amperage Rating	20 A
Frequency Rating	50/60 Hz

## Certifications and Compliance

CSA File Number	LR11712
Hazardous Rating(s)	<ul style="list-style-type: none"> <li>• Class I, Divisions 1 &amp; 2, Groups C, D</li> <li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li> <li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li> <li>• Class III, Divisions 1 &amp; 2</li> </ul>
Nema Rating	3
UL File Number	E53360, E10501

## Product Assets

[Catalogs - Killark Catalog](#)  
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
KILL\_CA-FXS-GFI-1020-SPEC-EN | REV 1/2024