



## **G Series Extended Maintained Contact 2-Position Selector Switch Operator - "Off - On"/Blank Nameplate - 2NO Contact Rating**

By Killark  
Catalog # [GOL52A6](#)

Killark GO SERIES Operators are a component use in conjunction with a Hazardous Location enclosure to provide control solutions in for; START/STOP Motor Functions, LED Pilot Light Indications and more. Utilized in Class 1 Division 1 & 2, Class 1 Zone 1 & 2 areas for indoor and outdoor use. UL Listed and CSA Certified.



\*Representative Image

Features

- 
- 
- 
- 

Application

G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures.

General

Action	Rotary
Actuator	2 Position Selector Switch
Ambient Temp. Range	UL: -25 to 40 °C, CSA: -50 to 40 °C, IEC: -20 to 40 °C
Catalog Number	GOL52A6
Color	Black
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	1
Series	GO
Type	Selector Switch
UPC	783936399447

Dimensions

Dimensions	6.31 in x 2.25 in x 1.25 in
Gross Weight with Packaging	1
Height	1.25 in
Length	6.31 in
Width	2.25 in

Electrical Ratings

Amperage Rating	10 A
Contact Rating	60A INRUSH @ 120 VAC; 30A INRUSH @ 240 VAC; 15A

INRUSH @ 480 VAC; 12A  
INRUSH @ 600 VAC; 0.55A  
INRUSH @ 125 VDC; 0.275A  
INRUSH @ 250 VDC; 6A  
BREAKING @ 120 VAC; 3A  
BREAKING @ 240 VAC; 1.5A  
BREAKING @ 480 VAC; 1.2A  
BREAKING @ 600 VAC; 0.55A  
BREAKING @ 125 VDC; 0.275A  
BREAKING @ 250 VDC; 10A  
CARRYING @ 120 VAC; 10A  
CARRYING @ 240 VAC; 10A  
CARRYING @ 480 VAC; 10A  
CARRYING @ 600 VAC; 2.5A  
CARRYING @ 125 VDC; 2.5A  
CARRYING @ 250 VDC.  
50/60 Hz

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups B, C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
Nema Rating	3, 4, 4X
UL File Number	E12379

Product Assets

- [Certifications - GO Series Operators CSA Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - GOL52A6 Specification Sheet French](#)
- [Specifications - G Series Selector Switches Specification Sheet](#)
- [Specifications - GOL52A6 Specification Sheet English](#)