



# HK Instrument Enclosure, 3-1/2 ID RD Body 3" DP & Flat Cover, Class I, II, III, BCDEFG, UL/CSA/FM, Cast Aluminum, Type 4,

By Killark  
Catalog # [HKB-B](#)

HK Series, 3-1/2 ID RD Body 3" DP & Flat Cover, Class I, II, III, BCDEFG, UL/CSA/FM, Cast Aluminum, Type 4, Instrument Enclosure.



\*Representative Image

## General

Application	
Catalog Number	HKB-B
Color	Gray
	Gris
Cover Type	Threaded
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Series	HK
Type	
UPC	783936295411

## Dimensions

Dimensions	6.5 in x 6.125 in x 4.75 in
Gross Weight with Packaging	3.04
Height	4.75 in
Length	6.5 in
Width	6.125 in

## Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups A(suffix GA) B, C, D
	Class I, Zones 1 & 2, Groups IIB+H2, IIA
	Class II, Divisions 1 & 2, Groups E, F, G
	Class III, Divisions 1 & 2
UL File Number	E83696

## Product Assets

- [Certifications - HK Series Terminal Enclosures UKCA Certificate](#)
- [Certifications - HK Series Enclosures UKCA Certificate](#)
- [Certifications - HK & HKBX Series Enclosures IECEx Certification](#)
- [Certifications - HK & HKBX Series Enclosures With Terminal Blocks IECEx Certification](#)
- [Certifications - HK Series Instrument Enclosures FM Certificate of Conformity](#)
- [Certifications - HK & HKBX Series Enclosures ATEX Certificate](#)
- [Certifications - HK & HKBX Series Enclosures With Terminal Blocks ATEX Certificate](#)
- [Certifications - HK & HKBX Series CSA Certificate of Compliance](#)
- [Certifications - HK & HKBX Series Enclosures Declaration of Conformity](#)
- [Certifications - HK & HKBX Series Enclosures with Terminal Blocks IECEx Certification \(Increased Safety\)](#)
- [Certifications - HK & HKBX Series Enclosures UL Certification](#)
- [Certifications - HK & HKBX Series Enclosures With Terminal Blocks Declaration of Conformity](#)
- [Certifications - HK & HKBX Series Enclosure With Terminal Blocks ATEX Certificate \(Increased Safety\)](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - HKB Series IOM K1232](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
KILL\_CA-HKBB-SPEC-EN | REV 6/2024