



**KFS400-76 - KF Series - Aluminum
400 Watt High Pressure Sodium
Marine Floodlight(Lamp Not
Included) - Quadri-Volt
(120/208/240/277V) At 60Hz**

By Killark
Catalog # [KFS400-76](#)

KF Series - Aluminum 400 Watt High Pressure Sodium Marine Floodlight(Lamp Not Included) - Quadri-Volt (120/208/240/277V) At 60Hz

Features

- Rugged weathertight housing of copperfree aluminum with corrosion resistant bronze finish
- Wide beam distribution
- Thermal shock, impact-resistant lens
- Continuous silicone gasketing
- All external hardware is corrosion resistant including HubbellGard® ceramic coated screws
- Trunnion mounting-heavy gauge, hot dip galvanized steel mounting with stainless steel hardware
- 3/4" NPT entry on back lower left

Application

KF Series floodlights can be used in industrial installations where flammable gases or vapors may exist due to abnormal conditions resulting in the creation of a Class I, Div. 2 hazardous location as defined by the NEC. Also can be used where general corrosive atmospheric conditions exist such as ocean piers, marinas, and costal areas. Designed for heavy duty applications where long life and maintenance-free service are essential.

General

Catalog Number	KFS400-76
Color	Bronze
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Mogul Base
Light Source	High Pressure Sodium
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Trunnion
Number of Lamps	0
Optic Type	Glass Lens
Series	KF



Type	Aluminum High Pressure Sodium Floodlight
UPC	783936384153

Dimensions

Dimensions	18.125 in x 10.125 in x 23.25 in
Gross Weight with Packaging	40.16
Height	23.25 in
Length	18.125 in
Width	10.125 in

Electrical Ratings

Frequency Rating	60 Hz
Initial Lumens	50000
Voltage Rating	Quad - 120/277/347/480 VAC
Wattage	400 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2, Groups A, B, C, D• Class I, Zone 2, Groups IIC, IIB, IIA• Class II, Division 2, Groups F, G• Class III, Divisions 1 & 2
---------------------	---

Product Assets

- [Certifications - KF Series CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_KFS40x-76](#)
- [Specifications - KFS40076 Specification Sheet English](#)
- [Specifications - KFS400-76 Specification Sheet French](#)
- [Specifications - KF Series Floodlights Specification Sheet](#)