

# NOR-2.5S

NONI 2.5" SQUARE RECESSED FAMILY

## ORDERING GUIDE

Examples: NOR-2.5SDL-NHN-SO930K-DM1NU / NOR-2.5SDS-TRM-FWHSRPPNON / NOR-2.5SDL-SO60

CATALOG #

### HOUSING

NOR-2.5S					
Series/Category/Size/Shape	Function	Housing	Optic Type	CRI/CCT	Driver Options
NOR-2.5S Noni Recessed Family 2.5" Square	DL Downlight	NHN New Construction Housing, Non-IC  NHI New Construction Housing, IC  CP Chicago Plenum	HO High-CBCP Optic <sup>1</sup>	927K 90 CRI, 2700K	DM1 0-10V, ELV, TRIAC 1% ERP 0-10V, ELV, TRIAC Dim-to-Dark
	LWD Lensed Wall Wash, Deep		LW Wall Wash Optic <sup>2</sup>	930K 90 CRI, 3000K	
	LWS Lensed Wall Wash, Shallow		SO Ultra-Smooth Optic	935K 90 CRI, 3500K	
	AA Adjustable Accent			940K 90 CRI, 4000K	
				830K 80 CRI, 3000K	
				835K 80 CRI, 3500K	

Control Options	U Voltage	Accessories
N None	U Universal Voltage 120-277V	RMB Residential Mounting Bars
LV Lutron Vive 0-10V, 120-277V		
LVE Lutron Vive EcoSystem		

### TRIM

NOR-2.5S		TRM			
Series/Category/Size/Shape	Function	Housing	Reflector Flange Color	Reflector Insert Color	Reflector Lens
NOR-2.5S Noni Recessed Family 2.5" Square	DS Downlight, Shallow (5/8" - 1 1/4" ceiling) DD Downlight, Deep (1 1/4" ceiling only) LWD Lensed Wall Wash, Deep LWS Lensed Wall Wash, Shallow AA Adjustable Accent	TRM Trim	FWHS White	Texture	CLR Clear <sup>3</sup>
			FGYS Gray		RWH White
			FBLS Black	RGY Gray	HEX Hex Cell Louver <sup>3</sup>
			FAMW Anti-Microbial White	RBL Black	NON No Lens <sup>3</sup>
			FX Custom Finish	RGT Graphite	SOL Solite <sup>3</sup>
			FT Flangeless	RPP Pink Panache	
			FCOS Copper	RGH Grasshopper	
				Smooth	
				RWHS White	
				RGYS Gray	
	RBL Black				
	RCOS Copper				
	RAMW Anti-Microbial White				
	Other				
	RX Custom Finish				

### OPTIC

NOR-2.5S		
Series/Category/Size/Shape	Function	Optic/Beam
NOR-2.5S Noni Recessed Family 2.5" Square	DL Downlight	Ultra-Smooth Optic
	LWD Lensed Wall Wash, Deep	SO60 60°
	LWS Lensed Wall Wash, Shallow	Wall Wash Optic
	AA Adjustable Accent	LWLW Lensed Wall Wash <sup>2</sup>

Notes:

- 1 Available only when "AA" function selected
- 2 Available only when "LW" function selected
- 3 For AA only
- 4 FRS must be spec for DL/LW