



# VML-X Series LED Area light 250 Watt, 120-277VAC, 28000 Lumen 1¼" 25° Stanchion Mount

By Killark  
Catalog # [VML3X2830D4G](#)



The VML-X Series is an Area Light fixture using energy efficient LED's. The redesigned CertiLite VML-X uses optics on the LED's to direct the light to where it is needed. This fixture is made with a cast copper-free aluminum housing and mount that is suitable for harsh and hazardous environments. The design of this fixture internal heat sink keeps a clean look on the outside of the fixture creating a LED fixture that does not contain external heat fins. Easily Retro fit any old HID or LED fixture to the new VML-X for a cleaner more efficient light.

## Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

## Application

- Class I Division 2 Hazardous Locations
- Class II Hazardous Dust
- Zone 2 Hazardous Locations
- Off and On Shore Oil and Gas
- Wet and Marine Locations
- Food and Beverage
- Heavy Industrial

## General

Color Temperature	5000 K
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	23,000 - 28,000 lm
Lumens	28000
Mounting Type	25° Stanchion
Optic Type	Glass Globe
Series	VML-X

## Dimensions

Hub Size	1-1/4"
----------	--------

## Electrical Ratings

Current / Amperage Rating	2.08-0.09 A
Frequency Rating	50-60 Hz
Voltage Rating	120-277 VAC
Wattage	250 W

## Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"> <li>• Class I, Div2, Groups A,B,C,D</li> <li>• Class I, Zone 2, Groups IIC, IIB, IIA</li> <li>• Class II, Div. 1&amp;2, Groups E,F,G</li> <li>• IECEx QPS 15.0006</li> <li>• Ex ec IIC T4/T3 Gc</li> <li>• Ex tb IIIC T4/T3 Db</li> <li>• QPS 22ATEX7000</li> </ul>
---------------------	--

## Product Assets

- [Catalog Page - LI\\_KIL\\_CP\\_EN\\_00043-CANFR](#)
- [Catalog Page - LI\\_KIL\\_CP\\_EN\\_00043-CANEN](#)
- [Catalog Page - VML-X Series Catalog Pages](#)
- [Certifications - VMLX & VM4L Series IECEx Certification](#)
- [Certifications - VMLX/VM4L Series EU Type ATEX Certificate](#)
- [Certifications - VMLX/VM4L Series ATEX Certificate](#)
- [Certifications - VMLX & VM4L Series Attestation of Conformity](#)
- [Certifications - VMLX Series QPS North American Certification](#)
- [Installation Manuals - VMLX Series IOM K1531](#)
- [Photometry - KIL\\_VML3X2830N](#)
- [Photometry - KIL\\_VML3X2830NDR](#)
- [Video](#)
- [Video](#)



A proud member of the Hubbell Family.