



# VML-X Series LED Area light 250 Watt, 120-277VAC, 28000 Lumen 1-1/4" 25° Stanchion Mount

By Killark  
Catalog # [VML3X2830D4G](#)



The VML-X Series is an Area Light fixture using energy efficient LED's. The redesigned CertiLite VML-X uses optics on the LED's to direct the light to where it is needed. This fixture is made with a cast copper-free aluminum housing and mount that is suitable for harsh and hazardous environments. The design of this fixture internal heat sink keeps a clean look on the outside of the fixture creating a LED fixture that does not contain external heat fins. Easily Retro fit any old HID or LED fixture to the new VML-X for a cleaner more efficient light.

## Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

## General

Application	
Catalog Number	VML3X2830D4G
Color Temperature	5000 K
Finish Type	Powder Epoxy Paint
Light Source	
Lumen Range	23,000 - 28,000 lm
Lumens	28000
Mounting Type	
Optic Type	Glass Globe
Series	VML-X

## Dimensions

Hub Size	1-1/4"
----------	--------

## Electrical Ratings

Current / Amperage Rating	2.08-0.09 A
Frequency Rating	50-60 Hz
Voltage Rating	120-277 VAC
Wattage	250 W

## Certifications And Compliance

Hazardous Rating(s)	Class I, Div2, Groups A,B,C,D
	Class I, Zone 2, Groups IIC, IIB, IIA
	Class II, Div. 1&2, Groups E,F,G
	IECEX QPS 15.0006
	Ex ec IIC T4/T3 Gc
	Ex tb IIIC T4/T3 Db
	QPS 22ATEX7000

## Product Assets

- [Brochures - VML-X Series Brochure](#)
- [Brochures - VML-X Series Brochure French](#)
- [Catalog Page - LI KIL CP EN 00043-CANEN](#)
- [Catalog Page - LI KIL CP EN 00043-CANFR](#)
- [Catalog Page - VML-X Series Catalog Pages](#)
- [Certifications - VMLX/VM4L Series EU Type ATEX Certificate](#)
- [Certifications - VMLX & VM4L Series Attestation of Conformity](#)
- [Certifications - VMLX & VM4L Series IECEx Certification](#)
- [Certifications - VMLX/VM4L Series ATEX Certificate](#)
- [Certifications - VMLX Series QPS North American Certification](#)
- [Installation Manuals - VMLX Series IOM K1531](#)
- [Photometry - KIL\\_VML3X2830NDR](#)
- [Photometry - KIL\\_VML3X2830N](#)
- [Video](#)
- [Video - VML-X Features and Benefits](#)
- [Video](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
KILL\_CA-VML3X2830D4G-SPEC-EN | REV 6/2024