

HUBBELL Power Systems

PDV-65 Optima Arrester (15.3 kV MCOV, 7314 Hardware)

By OHIO BRASS
Catalog # [2132657314](#)

IEEE Normal Duty Class / IEC Distribution Medium Polymer
Housed Surge Arrester



*Representative Image

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

Application	Distribution
Bracket Type	None
Cantilever Bending Strength - Max.	45 Nm
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359410171

Dimensions

Dimensions	9.313 in x 6.313 in x 4.750 in
Height	4.75 in
Length	9.313 in
Stud Type	3/8-16
Weight	2.3 lb
Width	6.313 in

Electrical Ratings

Creep and Leakage Distance	25.5 in (648 mm)
Current - Low Current Long	75 A
Duration (LCLD) Test	
Duty Cycle	18 kV
Frequency Rating	48-62 Hz
MCOV	15.3 kV
Maximum .5 Microsecond	59.7 kV
Discharge Volts @ Classifying Current	
Maximum Discharge Voltage	47.2 kV @ 1.5 kA
	50.3 kV @ 3 kA
	53.6 kV @ 5 kA
	60.3 kV @ 10 kA
	69.7 kV @ 20 kA
	87.1 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	42.2 kV
Minimum Strike	9.7 in
Pressure Relief Capability-Symmetrical rms (kA)	15
Time - Low Current Long	2000 Qs
Duration (LCLD) Test	

Logistics

Pallet Quantity	136
-----------------	-----

Product Assets

Brochures - Ohio Brass Sets the Standards for Arresters

Catalogs - Arresters IEEE & IEC Distribution Class

Installation Manuals - Installation Instructions for PDV/PVR

Arresters - Spanish

Installation Manuals - Installation Instructions for PDV/PVR

Arresters - Chinese

Installation Manuals - Installation Instructions for PDV/PVR

Arresters - French

Installation Manuals - PDV-PVR Polymer Distribution Class

Arrester Installation Instructions

ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc.

Effective 2020-2023, Multi-site (English)

ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.

Literature - Hubbell Arrester and Wildlife Guard Solution Kits

Literature - Lightning Surge Arresters

Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems

Sales Drawings - 2132657314 Drawing

Video - Hubbell Power Systems Metal Oxide Varistor



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-2132657314-SPEC-EN | REV 6/2024