

## PVR Optima (19.5 kV MCOV, 7224 Hardware)

By OHIO BRASS  
Catalog # 2216207224

IEEE Riser Pole Class Polymer Housed Surge Arrester



\*Representative Image

### Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

### Application

Distribution

### General

Bracket Type	NEMA 4x5 Crossarm Bracket
Cantilever Bending Strength - Max.	135 Nm
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359418566

### Dimensions

Height	14.7 in
Stud Type	3/8-16

### Electrical Ratings

Creep and Leakage Distance	30.8 in (782 mm)
Current - Low Current Long Duration (LCLD) Test	250 A
Duty Cycle	24 kV
Frequency Rating	48-62 Hz
MCOV	19.5 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	72.2 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> <li>• 55.5 kV @ 1.5 kA</li> <li>• 57.8 kV @ 3 kA</li> <li>• 60.2 kV @ 5 kA</li> <li>• 64.9 kV @ 10 kA</li> <li>• 71.7 kV @ 20 kA</li> <li>• 83.1 kV @ 40 kA</li> </ul>
Maximum Switching Surge Protective Level @ 500A	47.8 kV
Minimum Strike	11.3 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000 μs

### Certifications and Compliance

Industry Standard(s)	IEEE
----------------------	------

### Logistics

Pallet Quantity	80
-----------------	----

### Product Assets

[Catalogs - Arresters IEEE & IEC Distribution Class \(CA01065E\\_Catalog 70\)](#)  
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)  
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc. Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)  
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits \(SF14069E\)](#)  
[Video - Hubbell Power Systems Metal Oxide Varistor \(VI01022E0718\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
OB-2216207224-SPEC-EN | REV 1/2024