

# HUBBELL Power Systems

## PDV-65 Optima Arrester (17 kV Uc, CCAA Hardware)

By OHIO BRASS  
Catalog # [294017CCAA](#)

IEEE Normal Duty Class / IEC Distribution Medium Polymer  
Housed Surge Arrester



### Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

### General

Application	Distribution
Bracket Type	None
Color	Gray Housing
Material	ESP™ Polymer Housing
Type	Distribution

### Dimensions

Stud Type	M12
-----------	-----

### Electrical Ratings

Creep and Leakage Distance	25.5 in (648 mm)
Current - Low Current Long Duration (LCLD) Test	75A
Duty Cycle	21 kV
Frequency Rating	48-62 Hz
MCOV	17 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	67.2 kV
Maximum Discharge Voltage	53.2 kV @ 1.5 kA
	56.6 kV @ 3 kA
	60.3 kV @ 5 kA
	67.9 kV @ 10 kA
	78.5 kV @ 20 kA
	98.1 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	47.5 kV
Pressure Relief Capability-Symmetrical rms (kA)	15
Time - Low Current Long Duration (LCLD) Test	2000 Qs
Withstand Voltage - 60 Hz Wet	66.1
Withstand Voltage - Lightning Impulse	112.2

## Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters](#)

[Catalogs - Arresters IEEE & IEC Distribution Class](#)

[Installation Manuals - Installation Instructions for PDV/PVR](#)

[Arresters - Spanish](#)

[Installation Manuals - Installation Instructions for PDV/PVR](#)

[Arresters - Chinese](#)

[Installation Manuals - Installation Instructions for PDV/PVR](#)

[Arresters - French](#)

[Installation Manuals - PDV-PVR Polymer Distribution Class](#)

[Arrester Installation Instructions](#)

[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc.](#)

[Effective 2020-2023, Multi-site \(English\)](#)

[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)

[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)

[Literature - Lightning Surge Arresters](#)

[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)

[Video - Hubbell Power Systems In Depth: Distribution Arresters](#)

[Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
OB-294017CCAA-SPEC-EN | REV 6/2024