

PDV-100 Optima Arrester (17 kV Uc, CCBE Hardware)

By OHIO BRASS
Catalog # [294217CCBE](#)

IEEE Heavy Duty / IEC Distribution High Polymer Housed Surge
Arrester



*Representative Image

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Bracket Type	None
Catalog Number	294217CCBE
Color	Gray Housing
Material	ESP™ Polymer Housing
Type	Distribution

Dimensions

Stud Type	M12
-----------	-----

Electrical Ratings

Creep and Leakage Distance	28.1 in (713 mm)
Current - Low Current Long	250
Duration (LCLD) Test	
Duty Cycle	21 kV
Frequency Rating	48-62 Hz
MCOV	17 kV
Maximum .5 Microsecond Discharge Volts @ Classifying	71 kV

Current

Maximum Discharge Voltage	<ul style="list-style-type: none">• 51.4 kV @ 1.5 kA• 55 kV @ 3 kA• 58.2 kV @ 5 kA• 63.5 kV @ 10 kA• 72.1 kV @ 20 kA• 85 kV @ 40 kA
---------------------------	--

Maximum Switching Surge Protective Level @ 500A	47 kV
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000 Qs
Withstand Voltage - 60 Hz Wet Impulse	47.6
Withstand Voltage - Lightning Impulse	101.4

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters](#)
[Catalogs - Arresters IEEE & IEC Distribution Class](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese](#)
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Lightning Surge Arresters](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)
[Specifications - 294217CCBE](#)
[Video - Hubbell Power Systems Metal Oxide Varistor](#)
[Video - Hubbell Power Systems In Depth: Distribution Arresters](#)