

HUBBELL Power Systems

PDV-100 Optima Arrester (15.3 kV MCOV, 7224 Hardware)

By OHIO BRASS
Catalog # [2137157224](#)

IEEE Heavy Duty / IEC Distribution High Polymer Housed Surge
Arrester



*Representative Image

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Bracket Type	NEMA 4x5 Crossarm Bracket
Cantilever Bending Strength - Max.	80 Nm
Catalog Number	2137157224
Color	Gray Housing
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359374770

Dimensions

Dimensions	16.688 in x 9.250 in x 4.938 in
Height	4.938 in
Length	16.688 in
Stud Type	3/8-16
Weight	6.9 lb
Width	9.25 in

Electrical Ratings

Creep and Leakage Distance	25.2 in (640 mm)
Current - Low Current Long	250 A
Duration (LCLD) Test	
Duty Cycle	18 kV
Frequency Rating	48-62 Hz

MCOV	15.3 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	63.1 kV
Maximum Discharge Voltage	<ul style="list-style-type: none">• 45.6 kV @ 1.5 kA• 48.8 kV @ 3 kA• 51.7 kV @ 5 kA• 56.4 kV @ 10 kA• 64.1 kV @ 20 kA• 75.5 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	41.7 kV
Minimum Strike	8.8 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000 Qs

Logistics

Pallet Quantity	112
-----------------	-----

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters](#)
[Catalogs - Arresters IEEE & IEC Distribution Class](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese](#)
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Lightning Surge Arresters](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)
[Sales Drawings - 2137157224 \(Reference Only\)](#)
[Specifications - 2137157224](#)
[Specifications - Specification for IEEE Heavy Duty Class Distribution Arresters](#)
[Video - Hubbell Power Systems Metal Oxide Varistor](#)