

# HUBBELL Power Systems

## PVR Optima (15.3 kV MCOV, 7324 Hardware)

By OHIO BRASS  
Catalog # [2216157324](#)

IEEE Riser Pole Class Polymer Housed Surge Arrester



\*Representative Image

### Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

### General

Application	Distribution
Bracket Type	NEMA 4x5 Crossarm Bracket
Cantilever Bending Strength - Max.	135 Nm
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359261520

### Dimensions

Dimensions	22.188 in x 9.250 in x 4.938 in
Height	4.938 in
Length	22.188 in
Stud Type	3/8-16
Weight	5.2 lb
Width	9.25 in

### Electrical Ratings

Creep and Leakage Distance	26 in (660 mm)
Current - Low Current Long	250 A
Duration (LCLD) Test	
Duty Cycle	18 kV
Frequency Rating	48-62 Hz
MCOV	15.3 kV
Maximum .5 Microsecond	54.5 kV
Discharge Volts @ Classifying Current	
Maximum Discharge Voltage	41.8 kV @ 1.5 kA
	43.6 kV @ 3 kA
	45.4 kV @ 5 kA
	48.9 kV @ 10 kA
	54 kV @ 20 kA
	62.6 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	36 kV
Minimum Strike	9.7 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000 Qs

### Logistics

Pallet Quantity	112
-----------------	-----

## Product Assets

Brochures - Ohio Brass Sets the Standards for Arresters

Catalogs - Arresters IEEE & IEC Distribution Class

Installation Manuals - Installation Instructions for PDV/PVR

Arresters - Spanish

Installation Manuals - Installation Instructions for PDV/PVR

Arresters - Chinese

Installation Manuals - Installation Instructions for PDV/PVR

Arresters - French

Installation Manuals - PDV-PVR Polymer Distribution Class

Arrester Installation Instructions

ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc.

Effective 2020-2023, Multi-site (English)

ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.

Literature - Hubbell Arrester and Wildlife Guard Solution Kits

Literature - Lightning Surge Arresters

Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems

Sales Drawings - 2216157324 (Reference Only)

Video - Hubbell Power Systems Metal Oxide Varistor



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
OB-2216157324-SPEC-EN | REV 6/2024