

**HV PRC Polymer Bushing - 138kV**

By PCORE Electric  
Catalog # [PRC650P1216RS](#)

PRC® 138kV-1200A / 1600A Transformer-Circuit Breaker  
Polymer Bushing, Paper-Resin-Capacitor Type, Rated per IEEE  
C57.19.01, Bottom connected for Air-to-Oil Applications, 23.00"  
Min. Oil Immersion Level

**Features**

- Resin-impregnated paper wound core with external polymer (silicon) insulator
- High creep upper porcelain, High seismic, oil free

**Application**

Transformer-Oil Circuit Breaker

**General**

Catalog Number	PRC650P1216RS
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	Polymer (Silicon)
Mounting Position	Vertical
Number of Bolt Holes - Bottom Terminal	4, 8
Number of Flange Mounting Holes	6
Test Tap	Yes
Top Terminal Plating	Silver Plated
Top Terminal Type	Threaded
Type	Condenser Bushings

**Dimensions**

Above Flange Length	81.38 in
Below Flange Length	46.75 in
Diameter - Below Flange	8.00 in
Maximum P	
Diameter - Bottom Terminal Bolt Circle	3.75 in, 6.75 in
Diameter - Bottom Terminal Bolt Holes	3/8-16, 1/2-13
Diameter - Bottom Terminal Outside	7.75 in



Diameter - Live Part Top	10.63 in
Effective Length - Top Terminal	2.00 in
Flange Mounting Hole Bolt Circle	14.25 in
Flange Mounting Hole Diameter	1.25 in
Flange Outside Diameter	16.25 in
Length	128.13 in
Length - Ground Shield	23.00 in
Length - Minimum Oil Immersion Level	23.00 in
Thread Size - Bottom Terminal	3/8-16, 1/2-13
Thread Size - Drawlead	1 1/4-12
Connector	
Weight	390 lb

**Electrical Ratings**

BIL	650 kV
Current Rating	1200A / 1600 A
Minimum Creepage	215 in
Minimum Strike	61 in
kV Class	138 kV

**Certifications And Compliance**

Industry Standard(s)	IEEE
----------------------	------

**Product Assets**

[Brochures - Expanded Quick Selection Guide - HPS Power Apparatus Bushings](#)  
[Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)  
[Installation Manuals - Instruction Manual for Oil-Free PRC® Bushings with Polymer Insulator](#)  
[Literature - INTRODUCING PCORE® OIL-FREE HIGH VOLTAGE PRC® BUSHINGS](#)  
[Sales Drawings - PRC650P1216RS](#)  
[Specifications - PRC650P1216RS](#)