




# CFB2G & CFB4G Rectangular Series, Flush Furniture Feed Cover Assembly, Aluminum Powder Paint Finish

By Hubbell Premise Wiring  
Catalog # [24GTFFCVRALU](#)



Concrete Floors, Recessed, CFB2G & CFB4G Rectangular Series, Flush Furniture Feed Cover Assembly, Aluminum Powder Paint Finish

## Features

- Flush Style Cover
- (1) 2" Conduit Hub and (1) 3/4" Conduit Hub
- Die Cast Aluminum Cover Construction for Enhanced Durability
- Meets UL 514A Scrub Water Requirements
- ADA Compliant

## Application

For Use with Concrete Floor Boxes

## General

|                              |   |
|------------------------------|---|
| Application - For Use On     | Concrete                                |
| Color                        | Aluminum Powder Coat                    |
| Construction                 | Cast                                    |
| Construction Material - Main | Metallic                                |
| Cover Shape                  | Rectangle                               |
| Cover Type                   | Rectangle                               |
| EU RoHS Indicator            | Contact Manufacturer                    |
| Finish Type                  | Aluminum                                |
| Material                     | Cast Aluminum                           |
| Mounting Method              | Mounts to Box                           |
| Mounting Type                | (4) Screw Mount                         |
| Number of Gang(s)            | 2-Gang                                  |
| Series                       | Recessed - CFB Series                   |
| Size                         | Standard Sized Product                  |
| Sub Brand                    | Concrete Floor Boxes                    |
| Type                         | Furniture Feed Concrete Floor Box Cover |
| Type of Use                  | Tile/Flush, Furniture Feed              |
| Typical Application          | Tile/Flush, Furniture Feed              |
| UPC                          | 783585526935                            |

## Dimensions

|        |          |
|--------|----------|
| Length | 10.69 in |
| Width  | 6.19 in  |

## Conductor Related

|             |                   |
|-------------|-------------------|
| Cable Entry | (2) Threaded Hubs |
|-------------|-------------------|

## Certifications and Compliance

|                      |   |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"><li>• cULus</li><li>• UL514</li></ul> |
|----------------------|---|

## Product Assets

[Catalog Page - PREM R9 Catalog Page](#)  
[Catalog Page - PREM R7 Catalog Page](#)  
[Catalog Page - PREM R8 Catalog Page](#)  
[Catalogs - HPW CATALOG\\_2023\\_FULL](#)

## Related Products

[CFB2G25CR - 2-Gang CFB Series Box for Rectangular Covers, 2.50" Minimum Depth of Pour, Corrosion Resistant Paint](#)  
[CFB4G30CI - Recessed 4-Gang Concrete Floorbox with Rectangular Cover.](#)  
[CFB2G30 - 2-Gang CFB Series Box for Rectangular Covers, 3.00" Minimum Depth of Pour](#)  
[CFB4G30CR - 4-Gang CFB Series Box for Round Covers, 3.75" Minimum Depth of Pour](#)  
[CFB4G25CR - 4-Gang CFB Series Box for Rectangular Covers, 2.50" Minimum Depth of Pour, Corrosion Resistant Paint](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM-24GTFFCVRALU-SPEC-EN | REV 7/2023