



CFB2G & CFB4G Rectangular Series, Flush Furniture Feed Cover Assembly, Black Powder Paint Finish

By Hubbell Premise Wiring
Catalog # [24GTFFCVRBK](#)



Concrete Floors, Recessed, CFB2G & CFB4G Rectangular Series, Flush Furniture Feed Cover Assembly, Black Powder Paint Finish

Features

- Flush Style Cover
- (1) 2" Conduit Hub and (1) 3/4" Conduit Hub
- Die Cast Aluminum Cover Construction for Enhanced Durability
- Meets UL 514A Scrub Water Requirements
- ADA Compliant

Application

For Use with Concrete Floor Boxes

General

Application - For Use On	Concrete
Color	Black Powder Coat
Construction	Cast
Construction Material - Main	Metallic
Cover Shape	Rectangle
Cover Type	Rectangle
EU RoHS Indicator	Contact Manufacturer
Material	Cast Aluminum
Mounting Method	Mounts to Box
Mounting Type	(4) Screw Mount
Number of Gang(s)	2-Gang
Series	Recessed - CFB Series
Size	Standard Sized Product
Sub Brand	Concrete Floor Boxes
Type	Furniture Feed Concrete Floor Box Cover
Type of Use	Tile/Flush, Furniture Feed
Typical Application	Tile/Flush, Furniture Feed
UPC	783585446509

Dimensions

Length	10.69 in
Width	6.19 in

Conductor Related

Cable Entry	(2) Threaded Hubs
-------------	-------------------

Certifications and Compliance

Industry Standard(s)	UL 514
----------------------	--------

Product Assets

[Catalog Page - PREM R9 Catalog Page](#)
[Catalog Page - PREM R7 Catalog Page](#)
[Catalog Page - PREM R8 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)

Related Products

[CFB4G30CR - 4-Gang CFB Series Box for Round Covers, 3.75" Minimum Depth of Pour](#)
[CFB4G30CI - Recessed 4-Gang Concrete Floorbox with Rectangular Cover.](#)
[CFB4G30 - 4-Gang CFB Series Box for Rectangular Covers, 3.00" Minimum Depth of Pour](#)
[CFB2G30CR - 2-Gang CFB Series Box for Rectangular Covers, 3.00" Minimum Depth of Pour, Corrosion Resistant Paint](#)
[CFB2G25CR - 2-Gang CFB Series Box for Rectangular Covers, 2.50" Minimum Depth of Pour, Corrosion Resistant Paint](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-24GTFFCVRBK-SPEC-EN | REV 7/2023