

# HUBBELL Premise Wiring

## LC Fiber Trunk Cable Assembly, 10 Feet

By Hubbell Premise Wiring  
Catalog # [FFPLC12M4L10FN](#)

12-Fiber Plenum Rated Type A OM4 LC Fiber Trunk Cable Assembly, 10 Feet



### Features

- Factory terminated and tested for simple installation
- Customizable length, color, and cable construction
- Easily migrate to 100G, 200G, and beyond
- Built with Corning ClearCurve Fiber
- Premium low loss connector options for all applications
- Made in USA

### Application

Fiber Data Connectivity

### General

|                    |                |
|--------------------|----------------|
| Catalog Number     | FFPLC12M4L10FN |
| Color              | Aqua           |
| Connector Type     | LC             |
| Material           | PVC            |
| Series             | FIBERHUBB™     |
| Size               | 0.12           |
| Style              | LC             |
| Temperature Rating | 0 °C to 70 °C  |
| Type               | Trunk Cable    |
| UPC                | 662620367576   |

### Dimensions

|                 |         |
|-----------------|---------|
| Length          | 10 in   |
| Length (Meters) | 3.048 m |

### Conductor Related

|                  |               |
|------------------|---------------|
| Fiber Type       | OM4           |
| Mode             | Multimode     |
| Number of Fibers | 12            |
| Wire Type        | Multimode OM4 |

### Certifications And Compliance

|                      |   |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"><li>• GR-326</li><li>• Telcordia</li><li>• ANSI/TIA-568-D</li><li>• RoHS</li><li>• UL 94 V-0</li><li>• NFPA 270</li></ul> |
|----------------------|---|

### Product Assets

- [Literature - Quick Turn Custom Fiber Trunk Assemblies Program](#)
- [Literature - Custom Fiber Trunk Assemblies](#)
- [Literature - Custom Fiber Trunk Assemblies FAQ](#)
- [Sales Drawings - HWS15232C](#)
- [Sales Drawings - HWS1533302C](#)
- [Sales Drawings - HWS1533301C](#)
- [Specifications - EP-PREM-TECH-CUSTOM-FIBER-TRUNK-ASSEMBLIES-SF-EN-2023-01122](#)
- [Specifications - PREMISE\\_FFPLC12M4L10FN\\_spec](#)
- [Video - Hubbell Premise Wiring - Fiber Optics Manufacturing Facility](#)
- [Video - FIBERHUBB MPO Trunk Assemblies](#)