



Category 6 Shielded Jack with Cobra-Lock™ Termination

By Hubbell Premise Wiring
Catalog # [HJS6EI](#)

NEXTSPEED® Shielded Category 6 is a tuned system of structured cabling components designed and balanced to work together to deliver Category 6A performance and headroom beyond 250MHz for 5GBASE-T assurance. NEXTSPEED® shielded provides the highest level of reliability in the industry with added protection against external noise and EMI.

Features

- Third Party Verified Category 6 Component
- Cobra-Lock™ Termination Reduces Termination Time by Over 75%
- Wires Secured Under Constant Compression
- Easily Re-Terminate
- Qualified to 150% of 802.3bt PoE Current Level

Application

Up to 5GBASE-T, 802.3bt POE

General

Color	Ivory
Construction Material - Main Contact	Diecast Zinc IDC: Phosphor Bronze with 100 Micro-Inch Tin Over Plating
Contact Point Material	Copper Alloy with Gold Over Plating
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Modular Jack with Cobra-Lock
Material - Housing	Diecast Zinc
Mounting Type	Snap-fit
Operating Cycles	750+ Plug & 25 Re-Termination Cycles
Performance	TIA Cat 6 Component, Third Party Verified
Series	Cat 6 Shielded
Size	0.87 (22) x 0.67 (17) x 1.39 (35)
Style	RJ-45 Jack
Sub Brand	Cobra-Lock
Temperature Rating	Max Continuous- 75° C, Minimum- -40° C Without Impact
Type	Modular Jack with Cobra-Lock
UPC	662620666525



Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity RJ45 Jack to Cobra-Lock
Withstand Voltage 1,000 Vac @ 60 Hz

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• ANSI/TIA/EIA-568 Category 6 component• UL 1863 - Communications-Circuit Accessory• IEC60512-99-002 POE Disconnection Endurance• UL 2043 - Suitable for Air-Handling Spaces• RoHS Compliant
----------------------	--

Logistics

Carton Quantity 24
Number of Pieces in Package 1

Product Assets

[Catalog Page - PREM B4 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Customer Use Drawings - HWS14869C-HJS_SHIELDED_JACKS](#)
[Installation Manuals - HWS772024-Instruction_HJS_Shielded_Jack](#)
[Sales Drawings - HWS14869C-HJS_SHIELDED_JACKS](#)



A proud member of the Hubbell Family.