



Recessed 6" Series, Kit

By Hubbell Premise Wiring
Catalog # [S1R6PTACEHBRZ](#)

Fire Rated Poke Throughs, Recessed 6" Series, Kit, (1) S1R6PTFIT, (1) S1R6SPA, (1) S1R6SPC, (1) S1R6SPE, (1) S1R6SPH, (1) S1R6CVRBRZ



Features

- For use with a 6.00" to 6.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

Application

6" Fire-Rated Poke-Through Series

General

Accessory Type	6" FRPT Kit
Application - For Use On	Concrete
Color	Bronze
EU RoHS Indicator	Contact Manufacturer
Finish Type	Antique Bronze Plated Cover
Item Type	6" Recessed Fire-Rated Poke-Through Components
Material	Fabricated
Material - Mounting Hardware	Mounting Hardware Included
Mounting Type	6" Core Hole
Number Of Outlets	(2) 50% Left Side Sub Plates- (3) Extron® AAP Opening, (5) Extron® MAAP Opening, 50% Left Side, (1) Style Line® Decorator Opening, (2) Hubbell Keystone Openings and (1) 50% Left Side Sub Plate- (1) Style Line® Decorator Opening, (2) Hubbell Keystone Openings
Size	Standard Sized Product
Style	FRPT - Complete Kits
Sub Brand	SystemOne Recessed
Type	6" Recessed Rated Poke Through Kit
UPC	783585443386

Conductor Related

Cable Entry Through Cover

Certifications and Compliance

- Industry Standard(s)
- cULus Listed
 - Meets ADA Standards
 - UL 514A Listed

Product Assets

[Catalog Page - PREM R42 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs: 4, 6, 8 and 10 inch](#)
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)

Related Products

[S1FRPTJB - SystemOne Accessories, Junction Box](#)
[S1R6ADMTBK - Recessed 6" Series, Abandonment Plate, Black Powder Coat](#)
[S1R6DIV - Recessed 6" Series, Replacement Divider](#)
[S1R6PPT - Recessed 6" Series, Pre-Pour Tube](#)
[S1R6SPEXT - Recessed 6" Series, Sub Plate, 1.5" Extension Kit](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-S1R6PTACEHBRZ-SPEC-EN | REV 7/2023