



## Recessed 6" Series, Kit

By Hubbell Premise Wiring  
Catalog # [S1R6PTGRY](#)

Fire Rated Poke Throughs, Recessed 6" Series, Kit, (1)  
S1R6PTFIT, No Subplates, (1) S1R6CVRGRY



### Features

- For use with a 6.00" to 6.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

### Application

6" Fire-Rated Poke-Through Series

### General

Accessory Type	6" FRPT Kit
Application - For Use On	Concrete
Color	Gray
Construction	Fabricated
Construction Material - Main	6 Meunt
EU RoHS Indicator	Contact Manufacturer
Finish Type	Gray Powder Coat Cover
Item Type	6" Recessed Fire-Rated Poke-Through Components
Material	Fabricated
Material - Mounting Hardware	Mounting Hardware Included
Mounting Type	6" Core Hole
Size	Standard Sized Product
Style	FRPT - Complete Kits
Sub Brand	SystemOne Recessed
Type	6" Recessed Rated Poke Through Kit
UPC	783585590035

### Conductor Related

Cable Entry Through Cover

### Certifications and Compliance

- Industry Standard(s)
- cULus Listed
  - Meets ADA Standards
  - UL 514A Listed

### Product Assets

[Catalog Page - WDK P-17 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Catalogs - Premise Wiring Catalog](#)  
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)

### Related Products

[S1R6SPT - Recessed 6" Series, Sub Plate, 60% Left Side, \(2\) Extron® AAP Openings, \(4\) Extron® MAAP Opening](#)  
[S1R6SPC - Recessed 6" Series, Sub Plate, 50% Left Side, \(5\) Extron® MAAP Opening](#)  
[S1R6SPD - Recessed 6" Series, Sub Plate, 50% Left Side, \(3\) iSTATION Opening](#)  
[S1R6SPL - Recessed 6" Series, Sub Plate, 50% Left Side, \(3\) Extron® AAP Opening, \(2\) Hubbell Keystone Openings](#)  
[S1R6SPW - Recessed 6" Series, Sub Plate, 60% Left Side, \(2\) Style Line® Decorator Openings](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
PREM-S1R6PTGRY-SPEC-EN | REV 1/2024