



## Recessed 6" Series, Kit

By Hubbell Premise Wiring  
Catalog # [S1R6PTWZALU](#)

Fire Rated Poke Throughs, Recessed 6" Series, Kit, (1) S1R6PTFIT, (1) S1R6SPW, (1) S1R6SPZ, (1) S1R6CVRALU



### Features

- For use with a 6.00" to 6.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

### Application

6" Fire-Rated Poke-Through Series

### General

Accessory Type	6" FRPT Kit
Application - For Use On	Concrete
Color	Aluminum
EU RoHS Indicator	Contact Manufacturer
Finish Type	Brushed Aluminum Cover
Item Type	6" Recessed Fire-Rated Poke-Through Components
Material	Fabricated
Material - Mounting Hardware	Mounting Hardware Included
Mounting Type	6" Core Hole
Number Of Outlets	(1) 60% Left Side Sub Plate- (2) Style Line® Decorator Openings and (1) 40% Right Side Sub Plate- (2) 20A Pre-Wired Receptacles, 1 Circuit, 18" Leads
Size	Standard Sized Product
Style	FRPT - Complete Kits
Sub Brand	SystemOne Recessed
Type	6" Recessed Rated Poke Through Kit
UPC	783585443270

### Conductor Related

Cable Entry Through Cover

### Certifications and Compliance

- Industry Standard(s)
- cULus Listed
  - Meets ADA Standards
  - UL 514A Listed

### Product Assets

[Catalog Page - PREM R42 Catalog Page](#)  
[Catalogs - HPW CATALOG\\_2023\\_FULL](#)  
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs: 4, 6, 8 and 10 inch](#)  
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)

### Related Products

[S1FRPTJB - SystemOne Accessories, Junction Box](#)  
[S1R6SPEXT - Recessed 6" Series, Sub Plate, 1.5" Extension Kit](#)  
[S1R6DIV - Recessed 6" Series, Replacement Divider](#)  
[S1R6ADMTBK - Recessed 6" Series, Abandonment Plate, Black Powder Coat](#)  
[S1R6PPT - Recessed 6" Series, Pre-Pour Tube](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM-S1R6PTWZALU-SPEC-EN | REV 7/2023