



Double Ended Cobra-Lock™ Coupler

By Hubbell Premise Wiring
Catalog # [SC6A](#)



The Cobra-Lock™ Coupler gives installers a quick and reliable method to extend a run or fabricate single-ended MTPL cords for applications like wireless APs or IP cameras. Designed to perform in Cat 6A channels, the coupler can be used in shielded or UTP systems and is backward compatible to Cat 6 and Cat 5e applications.

Features

- Preterminated to Cat 6A FTP bootless Patch Cord
- Cobra-Lock™ Termination Provides Speed and Reliability
- Provided with Mount-Anywhere Clip
- Cat 6A Channel Compliant
- Built From Plenum Rated Components

Application

Up to 10GBASE-T, 802.3bt POE

General

Color	<ul style="list-style-type: none"> • Silver • Silver
Construction Material - Main Contact	Diecast Zinc IDC: Phosphor Bronze with 100 Micro-Inch Tin Over Plating
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Coupler
Material - Housing	Diecast Zinc
Mounting Type	Mount Anywhere Clip
Performance Series	TIA Cat 6A Channel Compliant Cat 6A Shielded
Size	0.92 (23) x 0.66 (17) x 1.65 (42)
Style	Cobra-Lock Coupler Accessory
Sub Brand Type	Cobra-Lock <ul style="list-style-type: none"> • Coupler • Coupler
UPC	662620344263

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity Cobra-Lock to Cobra-Lock
Withstand Voltage 1,000 Vac @ 60 Hz

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • ANSI/TIA/EIA-568 Category 6A channel • UL 1863 - Communications-Circuit Accessory • UL 2043 - Suitable for Air-Handling Spaces • RoHS Compliant
----------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Logistics

Carton Quantity	24
Number of Pieces in Package	1

Product Assets

[Catalog Page - PREM A4 Catalog Page](#)
[Catalog Page - PREM B6 Catalog Page](#)
[Catalog Page - PREM A5 Catalog Page](#)
[Catalogs - HPW CATALOG_2023_FULL](#)
[Installation Manuals - HWS772137-Instructions](#)
[Literature - Premise MPTL Assembly with Cobra-Lock Termination](#)
[Literature - netSELECT Category 6A End to End UTP System](#)
[Sales Drawings - HPW_SC6A_DRAWING_PDF](#)

Related Products

[C6ASPD5B - Cable, NEXTSPEED, Category 6A, Discontinuous Shield, 23 AWG, Reel in Box, UTP, Plenum, Blue](#)
[HCL6AB10 - Patch Cord, NEXTSPEED, Category 6A, Low Diameter 28 AWG, Blue, 10 Foot](#)
[HC6AB10 - Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 10' Length, Blue](#)
[C6ASRDSB - Cable, NEXTSPEED, Category 6A, Discontinuous Shield, 23 AWG, Reel in Box, UTP, Riser, Blue](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM-SC6A-SPEC-EN | REV 7/2023