



POINT DUME® by Jeffrey Alan Marks for Progress Lighting Shadmore Galvanized Finish Outdoor Hanging Pendant

By Progress Lighting
Catalog # [P550118-141](#)

Features

-
-
-
-
-
-
-
-
-
-

General

Can be mounted up or down	No
Catalog Number	P550118-141
Chain Qty	1 EA
Chain gauge	9 Gauge
Color	Gray
Color Generic	Grey
Construction Material - Main	Steel
Construction Material - Secondary	Aluminum
Construction Material - Secondary part	Inner Reflector, Socket Covers
Convertible fixture includes both mounts	No
Dusk to Dawn	No
EU RoHS Indicator	No
Finish Name	Galvanized Finish
Finish Type	Painted
Fire Resistance	No
Fixture Type	Outdoor Hanging
Glass	Marblized
Indoor/Outdoor	Indoor & Outdoor
Lamp Included	No
Lamp Shape	A19
Lamp Type	A19
Lamp Type Actual	A19
Lamp Type Basic	Incandescent
Lifestyle	<ul style="list-style-type: none">• Modern• Modern Mountain• Industrial• Luxe• Transitional



Light Distribution
Mount location
Mounting Type
Mounting for outlet box included
New Products
Number of Lamps
Number of Lamps Total
Photocell
Post top fits standard
Power Source
Power Source Required?
Quick Install canopy
Quick Link connector
Room Type

• Urban Industrial
Ambient
Ceiling Chain
Ceiling
1/8 IP Mounting Plate

No
1
1
No
No
Hardwired
Yes
No
Yes

- Outdoor
- Patio
- Hall & Foyer
- Porch
- Great Room
- Living Room
- Dining Room
- Kitchen

On Website=Yes
Extra-Large
E26
Socket
Porcelain
Lantern
785247264643
1-year Limited Warranty

Service Life

Size Type
Socket Base Type - Main
Socket Type
Socket type material
Type
UPC
Warranty Length

Dimensions

Dimensions
Height
Length
Length - Installed
Note Weight of fixture exceeds NEC limits
Overall Length with Weight
Width
Width Diameter Descriptor

26 in x 26 in x 31.25 in
31.25 in
26 in
97.5 in
No
Overall Ht. W/Chain And Stem
19.95 lb
26 in
Extends

Electrical Ratings

Current Rating	0.5 A
Frequency Rating	60 Hz
Input Voltage	120 VAC
Lamp Wattage	100 W
Voltage Rating	120 VAC

Conductor Related

Wire Length	120 in
-------------	--------

Certifications And Compliance

Americans with Disabilities Act	No
Certified Listed	cETLus
Certified Listed Location	Damp Location Listed
DarkSky	No
ENERGY STAR Certified	No
Energy Efficient	No
JA8	No
Other Heavy Metal Content	No
Indicator	
Title 20	No

Title 22	No
Title 24	No

Logistics

Carton Quantity	1
-----------------	---

Resources

Instruction Sheet Number	93156780
--------------------------	----------

Product Assets

- [Applications Notes -](#)
- [PROG_Sizing_guideline_Front_Door_Hanging_Lantern_info](#)
- [Certifications - California Proposition 65 WARNING](#)
- [Finish Images - PROG_141_Galvanized-finish](#)
- [Installation Manuals - PROG_93156780_B_install](#)
- [Product Cross Section Image\(s\) - PROG_P550118-141dimensions_silo](#)
- [Product Logo - PROG_PL_Design_Series_logo_GOLD_logo](#)
- [Warranty - PROGRESS LIGHTING LIMITED WARRANTY](#)
- [Video](#)