

P300054-015-30

Description:

Inspired by the beauty of frozen ice forms, The Capelli Collection LED sconce features intriguing layers resulting in a sophisticated form. The integrated LED technology runs across the length of the fixture, allowing the illumination to showcase the unique effects of the handmade work of art. The back plate and knob details are finished in Chrome. Can be installed vertically or horizontally.

Specifications:

- Polished Chrome (-015) (plated)
- Steel Construction
- Clear Pattern glass Shade
- Inspired by the beauty of frozen ice forms
- The backplate and knobs are finished in Polished Chrome
- Its fashion-forward style complements Modern and Luxury interiors
- Mount horizontally or vertically on the wall in bath and vanity settings to enhance a spa-like atmosphere
- Measures 24in W x 4-3/4in ht.
- 39w integrated LED, 2,600 delivered lumens 72 lumens/watt, 3000K color temperature, 90+ CRI.
- ETL Safety listed for use in damp locations
- Compatible with many ELV dimmers
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box
- Mounting plate for outlet box included
- 6" of wire supplied
- Complies with "Americans with Disabilities Act" - ADA
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	36w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2600/72 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-30 °C
Max. Operating Temp	-30°C
Warranty	5 year limited warranty
Labels	cETLus Damp location listed Meets California Title 24 JA8-2016

Images:



Dimensions:

Width: 24"
 Depth: 3-3/4"
 Height: 4-3/4"
 H/CTR: 2-3/8" (glass facing up)

Glass
 Width: 24"
 Height: 3-7/16"

P300054-015-30

Dimming Notes:

is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron - NTELV-300

Lutron - DVELV-300P

Lutron - Caseta Wireless

Leviton – 6672

Leviton – 6674

Lutron - AYCL-153P

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton - AWRMG-EAW

Lutron - N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.