

#### Project:

Fixture Type:

Location:

Contact:

Four-Light Bath

Wall mounted • Damp location listed PROGRESS LED

#### **Description:**

Images:

Tubular etched glass shades pop against a geometric back plate to create Colonnade, an LED bath and vanity collection. Modern style and continuous illumination are ideal for a variety of bath and vanity settings - including Mid-Century and Luxe. LED source features 3000K and 90 CRI benefits, as well as a lifespan of more than 42,000 hours. Four-Light Bath in a Brushed Nickel finish.

#### **Specifications:**

- · Brushed Nickel (-009) (plated)
- Steel construction
- Etched White Glass Cylindrical
- Tubular etched glass shades pop against a geometric back plate in Colonnade
- 4-light 38-watt LED bath fixture
- · Colonnade is an LED bath and vanity collection
- · An integrated LED source provides a variety of energy and cost savings benefits for the homeowner
- Measures 31 3/8"W x 7 1/2" H
- 2026 lumens 52 lumens/watt (delivered)
- Warm white 3000K lighting color and 90+CRI
- Ideal for Mid-Century and Luxe environments
- + Dimmable with most Triac or ELV type dimmers
- Mount on wall in bath and vanity settings to enhance a spa-like atmosphere
- Shop the complete Colonnade LED collection for a coordinated look throughout your bath and vanity areas
- ADA compliant
- Damp location listed
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box
- Mounting plate for outlet box included
- 6" of wire supplied
- Complies with "Americans with Disabilities Act" ADA
- Meets California Title 24 JA8-2016

#### Performance:

Number of Modules	4
Input Power	38w per module
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	2026/52.2 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-10 °C
Warranty	5 year limited warranty
Labels	cETLus Damp location listed
	Meets California Title 24 JA8-2016



P300188-009-30

#### **Dimensions:**

Width: 31-3/8" Depth: 3-7/8" Height: 7-1/2" H/CTR: 3-7/8" (glass facing up)

Glass Width: 2-3/8" Length: 2-3/8" Height: 7-1/2"



## Four-Light Bath

Wall mounted • Damp location listed PROGRESS LED

### P300188-009-30

#### **Dimming Notes:**

P300188 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

# Dimming Controls Lutron - DVCL-253P Lutron - Caseta Wireless Leviton - 6672 Leviton - 6681

Lutron - AYCL-153P

Lutron - AYLV-600P

Lutron - NTLV-600

Lutron - N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.