

Project:
ixture Type:
ocation:
Contact:

Three-Light Bath

Wall mounted • Damp location listed PROGRESS LED

Description:

Tubular etched glass shades pop against a geometric back plate to create Colonnade, an LED bath and vanity collection. Modern style and continuous illumination are ideal for a variety of bath and vanity settings - including Mid-Century and Luxe. LED source features 3000K and 90 CRI benefits, as well as a lifespan of more than 42,000 hours. Three-Light Bath in a Brushed Nickel finish.

P300187-009-30

Images:

Specifications:

- · Brushed Nickel (-009) (plated)
- · Steel construction
- · Etched White Glass Cylindrical
- · Tubular etched glass shades pop against a geometric back plate in Colonnade
- · 3-light 28.5-watt LED bath fixture
- · Colonnade is an LED bath and vanity collection
- · An integrated LED source provides a variety of energy and cost savings benefits for the homeowner
- Measures 22"W x 7 1/2" H
- 1661 lumens 56 lumens/watt (delivered)
- Warm white 3000K lighting color and 90+CRI
- Ideal for Mid-Century and Luxe environments
- Dimmable with most Triac or ELV type dimmers
- · Mount on wall in bath and vanity settings to enhance a spa-like atmosphere
- Shop the complete Colonnade LED collection for a coordinated look throughout your bath and vanity areas
- · ADA compliant
- · Damp location listed
- Dimmable to 10% brightness (See Dimming Notes)
- · Back plate covers a standard 4" octagonal recessed outlet box
- Mounting plate for outlet box included
- · 6" of wire supplied
- Complies with "Americans with Disabilities Act" ADA
- Meets California Title 24 JA8-2016



Dimensions:

Width: 22" Depth: 3-7/8" Height: 7-1/2"

H/CTR: 3-7/8" (glass facing up)

Glass Width: 2-3/8" Length: 2-3/8" Height: 7-1/2"

Performance:

Number of Modules	3
Input Power	28.5w per module
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1661/56.9 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-10 °C
Warranty	5 year limited warranty
Labels	cETLus Damp location listed
	Meets California Title 24 JA8-2016



Three-Light Bath

Wall mounted • Damp location listed PROGRESS LED

P300187-009-30

Dimming Notes:

P300187 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron - DVCL-253P

Lutron - Caseta Wireless

Leviton - 6672

Leviton - 6681

Lutron - AYCL-153P

Lutron - AYLV-600P

Lutron - NTLV-600

Lutron - N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.