

One-Light LED Flush Mount

Ceiling mounted • Damp location listed



Description:

One-light 15 inch LED Flush Mount in Antiques Bronze features a white linen glass bowl. Fixtures are dimmable to 10 percent with Triac, phase forward or ELV dimmers. 3000K and 90 CRI.

Specifications:

- Antique Bronze (-020) (painted)
- Steel Construction
- Etched White Linen glass bowl
- 1389 lumens 50 lumens/watt (delivered)
- 3000k color temperature, 90+ CRI
- TM-21 54,000 hour life.
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	28w
Input Voltage	120 V
Input Frequency	50/60 Hz
Lumens/LPW (Source)	2409/88 (LM-82)
Lumens/LPW (Delivered)	1389/50 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	54,000 (L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-25 °C
Max. Operating Temp	25 °C
Warranty	5 year warranty
Labels	ETL Damp location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

P350007-020-30

Images:




Dimensions:

Diameter: 15"
Height: 5-7/8"

Progress Lighting

LED lighting facts®

A Program of the U.S. DOE

Light Output (Lumens)	1389
Watts	27.85
Lumens per Watt (Efficacy)	49.87
Color Accuracy	
Color Rendering Index (CRI) 90	
Light Color	
Correlated Color Temperature (CCT) 3000 (Bright White)	
	
All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.	
Visit www.lightingfacts.com for the Label Reference Guide.	
Registration Number: TH84-DR35R (9/13/2016) Model Number: P350007-020-30 Type: Luminaire - Decorative	

P350007-020-30

Dimming Notes:

P350007 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron NTELV-300

Leviton 6674

Lutron AYLV-600P

Lutron NTLV-600

Lutron MAELV-601

Leviton AWRMG-EAW

Lutron N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.