

Project:	
ixture Type:	
Location:	
Contact:	

One-Light LED Flush Mount

Ceiling mounted • Damp location listed PROGRESS LED



Description:

One-light 9-1/2 inch Square LED Flush Mount featuring a square Random Swirl glass bowl in a Brushed Nickel finish. Fixtures are dimmable to 10 percent with Triac or ELV dimmers. 3000K and 90CRI.

P350017-009-30

Images:

Specifications:

- Brushed Nickel (-009) (plated)
- Steel Construction
- Random Swirl glass diffuser
- · LED Module is replaceable (part # 93074038)
- 3000k color temperature, 90+ CRI
- · TM-21 60,000 hour life.
- · 1452 lumens 83 lumens/watt (source).
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" octagonal recessed outlet box
- · Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- · Meets California Title 24 JA8-2016



Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1452/83 (LM-82)
Lumens/LPW (Delivered)	1140/65.5 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016

Dimensions:

Square: 9-1/2" Height: 4-1/2"

Glass Width: 9-1/2" Length: 9-1/2" Height: 425"



One-Light LED Flush Mount

Ceiling mounted • Damp location listed PROGRESS LED



P350017-009-30

Dimming Notes:

P350017 is designed to be compatible with many NEMA SSL 7a Phase Cut (forward phase) dimmers as well as many ELV (reverse phase) controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Diva DVELV-300P

Lutron Nova T NTELV-300

Lutron Caseta

Lutron Ariadni AY-600P

Leviton Illumatech IPI06-1LZ

Lutron Lumea LG-603PG

Leviton SureSlide 6672

Leviton SureSlide 6674

Lutron Ariadni AYCL-153P

Lutron Skylark Contour CTCL-153P

Lutron Diva DVCL-153P

Pass & Seymour Harmony DCL453PTCCCV6

Lutron Toggler TGCL-153P

Lutron Maestro MACL-153M

Lutron Ariadni AYLV-600P

Lutron Maestro MA-600

Lutron NOVA T NTLV-600

lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Lutron Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.