

F	0	r	С	j	e	С	t		

Fixture Type:

Location:

Contact:

## Abide LED

## **Description:**

One-Light LED Flush Mount

### **Specifications:**

- Brushed Nickel (Plated)
- Steel Housing
- $\boldsymbol{\cdot}$  White PMMA Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Fixture covers a standard 4" recessed outlet box
- $\cdot$  6 in of wire supplied

#### **Performance:**

Input Power	16 W			
Input Voltage	120 VAC			
Input Frequency	60 Hz			
Lumens/LPW (Delivered)	1,062/65.6 (LM-79)			
ССТ	2700 К			
	3000 K			
	3500 K			
	4000 K			
	5000 K			
CRI	90 CRI			
Life (hours)	50000 (L70/TM-21)			
EMI/RFI	FCC Title 47, Part 15, Class B			
Warranty	5-year Limited Warranty			
Labels	cCSAus Damp Location Listed			
	Meets California Title 24 JA8-2022			






### **Dimensions:**

Diameter: 10-3/16 in Height: 2-3/4 in

White PMMA Diffuser Diameter: 9-1/4 in Height: 2-1/2 in



# P350274-009-CS



P350274-009-CS

FCC Title 47, Part 15, Class B

120 VAC

60 Hz

<25%

Yes\* Over-voltage, over-current, short-circuit protected \*See Dimming Notes for more information

Operating Temperature -30 °C to 30 °C

## Abide LED

**Photometrics:** 

ELECTRICAL DATA

Input Voltage

THD

EMI/RFI

Dimming

Input Frequency

## Ceiling Flush Mounted • Damp Location Listed PROGRESS LED

# P350274-009-CS



## **Dimming Notes:**

Abide LED

P350274-009-CS is designed to be compatible with many ELV/Reverse Phase Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

#### Dimming

Lutron NTELV-300
Lutron DVELV-300P
Lutron DVCL-253P
Lutron Caséta
Leviton 6672
Leviton 6674
Lutron AYCL-153P
Lutron SCL-153P
Lutron TGCL-153PH
Lutron MACL-153M
Eaton - AALO6

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

Controls:		
/-300		
/-300P		
-253P		
1		

## Ceiling Flush Mounted • Damp Location Listed PROGRESS LED

