

Three-Light LED Linear Chandelier

Ceiling mounted • Dry location listed



Description:

Moderna's modern-inspired silhouette provides a signature focal point for a variety of interior spaces. Features clear outer glass with an inner etched white glass shade and a sleek linear frame finished in Brushed Nickel. Replaceable AC LED module delivers energy-efficient illumination and long life performance.

Specifications:

- Brushed Nickel (-009) (plated)
- Steel Construction
- Clear glass shades, Etched White glass diffuser
- LED Module is replaceable (part # 93074036)
- Modern silhouette with a sleek linear frame.
- 670 lumens 71 lumens/watt (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 15 feet of wire supplied
- Two 6", eight 12" lengths of stem included
- Two pieces of six links of 9 gauge chain supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	3
Input Power	9w per module
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	670/71 (LM-82) per module
Lumens/LPW (Delivered)	623/69.2 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Dry location listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016

P400000-009-30

Images:



Dimensions:

Width: 5"
 Length: 32"
 Height: 16"
 Overall Ht. W/Stem: 82"

P400000-009-30**Dimming Notes:**

P400000 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Diva DVELV-300P

Lutron Nova T NTELV-300

Lutron Caseta

Lutron Ariadni AY-600P

Leviton Illumatech IPI06-1LZ

Leviton SureSlide 6672

Lutron Ariadni AYCL-153P

Lutron Skylark Contour CTCL-153P

Lutron Diva DVCL-153P

Lutron Toggler TGCL-153P

Lutron Maestro MACL-153M

Lutron Ariadni AYLV-600P

Lutron NOVA T NTLV-600

lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Lutron Renoir II AWRMG-EAW

Lutron Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.