

Project:
Fixture Type:

Location:

Contact:

**Box LED** 

Ceiling Mounted • Damp Location Listed PROGRESS LED



#### **Description:**

Foster a sophisticated atmosphere with this contemporary flush mount. A square, black frame attaches to a minimalist ceiling plate. A beautiful etched glass shade rests within the frame for a design sure to brighten any space with its fresh, elegant demeanor.

#### **Specifications:**

- · Etched glass Shade
- A beautiful etched glass shade rests within the frame for a design sure to brighten any space with its fresh, elegant demeanor.
- · A square, black frame attaches to a minimalist ceiling plate.
- Foster a sophisticated atmosphere with this contemporary flush mount.
- · Ideal for any hallway, foyer, stairway, or kitchen.
- · Perfect for transitional, modern, farmhouse, Craftsman, and contemporary settings.
- Measures 10-1/8-inch width by 4-1/4-inch height.
- · Uses one LED module (17w).
- · Compatible with many Triac/ELV dimmers (see dimming controls)
- · Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- Dimmable to 10% brightness (See Dimming Notes)
- Ceiling Pan covers a standard 4" recessed outlet box: 10.125 in W., 1 in ht., 10.125 in depth
- · Mounting backplate for outlet box included
- 6 in of wire supplied

#### **Performance:**

Number of Modules	1
Input Power	17 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1,276/73 (LM-82)
ССТ	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016


## P350114-031-30



#### **Dimensions:**

Square: 10-1/8 in Height: 4-1/4 in

Etched glass Shade Width: 8-7/8 in Height: 0-1/8 in





### **Box LED**

Ceiling Mounted • Damp Location Listed PROGRESS LED



#### **Dimming Notes:**

P350114-031-30 is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

# P350114-031-30

#### **Dimming Controls:**

Lutron Diva DVELV-300P

Lutron Nova T NTELV-300

Lutron Caseta

Lutron Ariadni AY-600P

Leviton Illumatech IPI06-1LZ

Lutron Lumea LG-603PG

Leviton SureSlide 6672

Leviton SureSlide 6674

Lutron Ariadni AYCL-153P

Lutron Skylark Contour CTCL-153P

Lutron Diva DVCL-153P

Pass & Seymour Harmony DCL453PTCCCV6

Lutron Toggler TGCL-153P

Lutron Maestro MACL-153M

Lutron Ariadni AYLV-600P

Lutron Maestro MA-600

Lutron NOVA T NTLV-600

lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Lutron Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.