

LED Flush Mount

 Ceiling mounted • Damp location listed **PROGRESS LED**


P350131-009-30

Description:

LED 15in. flush mount with white acrylic diffuser mounts to a Brushed Nickel ceiling pan. Ideal for ceiling or wall mount applications and suitable to add ambient illumination for Modern or Traditional interior spaces.

Specifications:

- Brushed Nickel (-009) (plated)
- Steel Construction
- Etched glass Bowl
- The classic ceiling fixture: A perfect dome with metallic rim
- They are good choices to brighten an entire room – ideal for ambient or general illumination
- The contoured, simple design makes it a fit across most styles, including Modern, Traditional and Transitional
- Brushed Nickel finish
- Measures 15in diameter x 5-1/4in ht.
- Contains one 26W LED Module 1,382 delivered lumens - 54 lumens/watt, 3000K color temperature, 90+ CRI.
- CSA Safety listed for use in damp locations
- Compatible with many ELV dimmers
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available
- Dimmable to 10% brightness (See Dimming Notes)
- Fixture covers a standard 4" octagonal recessed outlet box
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	26w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1770/68.07692307692308 (LM-82)
Lumens/LPW (Delivered)	1382/54 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30°C
Warranty	5-year limited warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

Images:



Dimensions:

Width: 15-1/4"
Height: 5-1/4"

Glass
Width: 14-1/4"
Height: 4-1/4"

P350131-009-30**Dimming Notes:**

P350131 is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron - Caseta Wireless

Leviton – 6672

Leviton – 6674

Lutron - AYCL-153P

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton - AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.