

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P500200-162 Point Dume™ - Surfrider

Like gentle waves lapping the sandy shore, the large Surfrider pendant has tiers of metal curves converging in an ever-widening circle. Oversized hooks suspended from a simple orb surround a floating braided metal cable, beautifully marrying form and function for an industrial meets modern-minded point of view. This family of fixtures is part of the Point Dume™ lighting collection which celebrates a curated mix of yesterday and today, distilling both industrial and artisanal influences. Malibblue, a soft blue-gray finish inspired by the love of the Malibu waves and sky, one of three signature finishes developed especially for the Point Dume™ Collection.



Diameter: 24-7/8 in
 Height: 26-1/2 in
 Overall Ht. W/Hooks and Chain: 103-1/2 in

- Tiers of metal overlap in a widening circle giving a triangular shape to the fixture, reminiscent of row upon row of gentle waves lapping the shoreline.
- Industrial details include a trio of oversized hooks surrounding the braided metal power cord and steel pinnings attaching the rows of metal on the body of the fixture, allowing for the light source to subtly gleam between each row.
- Inspired by the weathered terrain of the Malibu, California coastline.
- Stunning Malibblue finish gleams in a soft blue-gray neutral tone reminiscent of the waves and sky.
- Hang a single pendant over a breakfast nook table, desk in a home office or small kitchen island.
- Use in multiples over a large kitchen island, dining room table or entry foyer for a dramatic focal point and to coordinate a look across an open floor plan.
- Surfrider works well across several style palettes.
- Coastal, with the inspiration of waves on the shore adding a calming and relaxed feeling to a room.
- Modern, as its clean, crisp lines fit well with minimalist décor.
- Urban Industrial, as the use of galvanized steel lends a sense of unfinished rawness adding an element of industrial chic to the room.
- Offered in Malibblue, a soft blue-gray finish inspired by the love of the Malibu waves and sky, one of three signature finishes developed especially for the Point Dume™ Collection.
- Inside tiers are finished in a gleaming white.
- Large-scale three-light pendant with fixture diameter of 24-7/8 in. and height of 26-1/2 in.
- Chain adjustable, up to overall height 103-1/2 in.
- Use three 75w max. medium base incandescent or LED equivalent wattage bulbs (bulbs not included).
- For an alternate look, try Edison bulbs or other vintage-style filament bulbs (bulbs not included).
- Ceiling chain mounted, the chain is adjustable as necessary for the space.
- Six feet of nine in. gauge chain provided.

Category: Pendants
Finish: Malibblue (Plated)
Construction: Steel Construction

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mounted	Prewired	Quantity:	CCSAus Dry Location Listed
Mounting strap for outlet box included	15 feet of wire supplied	Three 75 W max. Medium Base or LED equivalent	1-year Limited Warranty
48 in of 9 gauge chain supplied	120 V	E26 base Porcelain sockets	

Canopy covers a standard 4" recessed outlet box: 6" W., 1.1875" ht., 6" depth