

# One-light Pendant

 Ceiling cord mounted • Damp location listed **PROGRESS LED**


## Description:

A distinctive classic globe pendant is accented by a striking metal polished chrome cap. The cap holds a beautiful opal glass shade ready to emit gentle illumination. This versatile pendant can be displayed as a single fixture or in groups of two or more to create a custom lighting design for your home.

## Specifications:

- Polished Chrome (-015) (Plated)
- Steel Construction
- Opal Glass Globe
- The cap holds a beautiful opal glass shade ready to emit gentle illumination.
- A distinctive classic globe pendant is accented by a striking metal polished chrome cap.
- This versatile pendant can be displayed as a single fixture or in groups of two or more to create a custom lighting design for your home.
- Ideal for any foyer, kitchen, or dining room.
- Perfect for mid-century modern, transitional, modern, or contemporary settings.
- Measures 11-5/8-inch width by 13-1/2-inch height.
- Overall length with cord is 136-1/2"
- Uses one LED bulb that is included (17w max).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting 1/8 IP Mounting Plate for outlet box included
- 10 feet of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

## Performance:

Number of Modules	1
Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1276/73 (LM-82)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-30 °C
Warranty	5-year limited warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

## P500148-015-30

## Images:



## Dimensions:

Diameter: 11-5/8"  
 Height: 13-1/2"  
 Overall Ht. W/Cord: 136-1/2"

Width: 11-5/8"  
 Height: 10-1/2"

**P500148-015-30****Dimming Notes:**

---

P500148 is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

**Dimming Controls**

---

Lutron Diva DVELV-300P

Lutron Nova T NTELV-300

Lutron Caseta

Lutron Ariadni AY-600P

Leviton Illumatech IPI06-1LZ

Lutron Lumea LG-603PG

Leviton SureSlide 6672

Leviton SureSlide 6674

Lutron Ariadni AYCL-153P

Lutron Skylark Contour CTCL-153P

Lutron Diva DVCL-153P

Pass & Seymour Harmony DCL453PTCCCV6

Lutron Toggler TGCL-153P

Lutron Maestro MACL-153M

Lutron Ariadni AYL-600P

Lutron Maestro MA-600

Lutron NOVA T NTLV-600

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Lutron Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.