

One-Light Outdoor

Project:

Fixture Type: Location:

Contact:

Post mounted • Wet location listed PROGRESS LED



P5445-3130K9

Westport LED offers traditional styling to complement a variety of home decor options. A durable die-cast aluminum frame cradles a softly diffused seeded glass shade. 3000K, 90+ CRI 623 lumens. One-light LED post mount. Black finish.

Specifications:

Description:

- Black (-31) (powder coat paint)
- Die-Cast Aluminum Construction •
- Etched Seeded glass shade .
- LED Module is replaceable (part # 93054049)
- Traditional styling.
- Softly diffused seeded glass shade. .
- . Complements many home decor styles with beaded detailing.
- 623 lumens 69.2 lumens/watt (source)
- 3000K color temperature, 90+ CRI.
- · Dimmable to 10% brightness (See Dimming Notes)
- 6" of wire supplied •
- ENERGY STAR[®] qualified •
- · Meets California Title 24 high efficacy requirements for outdoor use only

Performance:

Number of Modules	1	Dimen	
Input Power	9w		
Input Voltage	120 V	Diamete	
Input Frequency	60 Hz	Height:	
Lumens/LPW (Source)	623/69.2 (LM-82)		
Lumens/LPW (Delivered)	357/47.6 (LM-79)	Diffuser	
ССТ	3000 К	Width: 7 Length:	
CRI	90 CRI	Height:	
Life (hours)	60,000 (L70/TM-21)	Ū	
FCC	Meets FCC Title 47, Part 15 Class B		
Min. Start Temp	-30 °C		
Max. Operating Temp	30 °C		
Warranty	5 year warranty		
Labels	cCSAus Wet location listed		
	ENERGY STAR [®] qualified		
	Meets California Title 24 high efficacy requirements		
	for outdoor use only		





isions:

ter: 9" 16-3/8"

er 7" : 7" 5-3/4"



One-Light Outdoor



P5445-3130K9

Dimming Notes:

P5445 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron	Nova T	NTELV-300
Lutron	Vierti	VTELV-600
Lutron	Ariadni	AYCL-153P
Lutron	Diva	DVCL-153P
Lutron	Maestro	MAELV-600
Lutron	spacer/sys	stem SPSELV-600
Leviton	Renoir II	AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.