

# One-light LED Wall Lantern

 Wall mounted • Wet location listed **PROGRESS LED**


## Description:

A modern outdoor sconce with an open linear frame and seeded glass diffuser. Finished in Architectural Bronze. 624 lumens (source), 90+ CRI.

## Specifications:


- Architectural Bronze (-129) (painted)
- Aluminum Construction
- Clear Seeded glass diffuser
- LED Module is replaceable (part # 93074037)
- Modern outdoor sconce.
- Open linear frame.
- 624 lumens 66 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

## Performance:

|                        |  |
|------------------------|--|
| Number of Modules      | 1  |
| Input Power            | 9w   |
| Input Voltage          | 120 V  |
| Input Frequency        | 60 Hz  |
| Lumens/LPW (Source)    | 624/66 (LM-82)   |
| Lumens/LPW (Delivered) | 279/29.7 (LM-79)   |
| CCT                    | 3000 K   |
| CRI                    | 90+  |
| Life (hours)           | 60,000 (L70/TM-21)   |
| FCC                    | Meets FCC Title 47, Part 15 Class B  |
| Min. Start Temp        | -30 °C   |
| Max. Operating Temp    | 30 °C  |
| Warranty               | 5 year warranty  |
| Labels                 | cCSAus Wet location listed<br>ENERGY STAR® qualified<br>Meets California Title 24 JA8-2016 |

## P560029-129-30

## Images:



## Dimensions:

Width: 7-1/2"  
Depth: 4-3/4"  
Height: 16"  
H/CTR: 4-1/4"

**P560029-129-30****Dimming Notes:**

---

P560029 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

**Dimming Controls**

---

Lutron Diva DVELV-300P

Lutron Nova T NTELV-300

Lutron Caseta

Lutron Ariadni AY-600P

Leviton Illumatech IPI06-1LZ

Leviton SureSlide 6672

Lutron Ariadni AYCL-153P

Lutron Skylark Contour CTCL-153P

Lutron Diva DVCL-153P

Lutron Toggler TGCL-153P

Lutron Maestro MACL-153M

Lutron Ariadni AYL-600P

Lutron NOVA T NTLV-600

lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Lutron Renoir II AWRMG-EAW

Lutron Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.