

MEDIUM WALL LANTERN

Wall mounted • Wet location listed PROGRESS LED



P560055-031-30

Description:

Chandler features a traditional form that is equally appropriate for a modern bungalow or rustic farmhouse. The flared metal shade encloses a modern LED source with a domed glass diffuser. Full cutoff design provides Dark Sky compliance and energy-efficient illumination.

Specifications:

- Black (-031) (painted)
- Steel Construction
- Etched glass dome
- The flared metal shade encloses a modern LED source with a domed glass diffuser
- Full cutoff design provides Dark Sky compliance and energy-efficient illumination
- Design is equally at home on a modern bungalow or rustic farmhouse
- 670 lumens 71 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	9w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	670/71 (LM-82)
Lumens/LPW (Delivered)	474/51.5 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30° C
Warranty	5 year warranty
Labels	cCSAus Wet location listed ENERGY STAR® qualified Meets California Title 24 JA8-2016

Images:



Dimensions:

Width: 12"
Depth: 13"
Height: 11-1/2"
H/CTR: 3-3/4"

P560055-031-30

Dimming Notes:

P560055 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Diva DVELV-300P

Lutron Nova T NTELV-300

Lutron Caseta

Lutron Ariadni AY-600P

Leviton Illumatech IPI06-1LZ

Leviton SureSlide 6672

Lutron Ariadni AYCL-153P

Lutron Skylark Contour CTCL-153P

Lutron Diva DVCL-153P

Lutron Toggler TGCL-153P

Lutron Maestro MACL-153M

Lutron Ariadni AYL-600P

Lutron NOVA T NTLV-600

lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Lutron Renoir II AWRMG-EAW

Lutron Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.