

Project:			
Fixture Type:			
Location:			
Contact:			

# One-Light Pendant W/HAL AC LED Module

Ceiling cord mounted • Dry location listed PROGRESS LED



## **Description:**

The simple design of this LED Dome pendant offers complements a wide array of styles from industrial to farmhouse. The 9w LED pendant is 3000K in a White finish with a painted silver interior.

#### **Specifications:**

- · White (-30) (painted)
- · Aluminum Construction
- White, painted silver inside aluminum shade, White acrylic Diffuser
- LED Module is replaceable (part # 93054049)
- · Inspired to enhance modern home decor.
- · Complements a wide array of styles from industrial to farmhouse.
- White finish with a painted silver interior.
- · Dimmable to 10% with many ELV dimmers
- · 623 lumens 69.2 lumens/watt per module (source)
- · 3000K color temperature, 90+ CRI.
- · Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 10 feet of wire supplied
- · ENERGY STAR® qualified

#### **Performance:**

Number of Modules	1		
Input Power	9w		
Input Voltage	120 V		
Input Frequency	60 Hz		
Lumens/LPW (Source)	623/69.2 (LM-82)		
Lumens/LPW (Delivered)	388/51.7 (LM-79)		
ССТ	3000 K		
CRI	90+		
Life (hours)	60,000 (L70/TM-21)		
FCC	Meets FCC Title 47, Part 15 Class B		
Min. Start Temp	-30 °C		
Max. Operating Temp	30 °C		
Warranty	5 year warranty		
Labels	cCSAus Dry location listed		
	ENERGY STAR® qualified		

# P5340-3030K9

#### Images:



#### **Dimensions:**

Diameter: 10" Height: 5-5/8"

Overall Ht. W/Cord: 125-1/2"

Glass Width: 10" Length: 10" Glass 2 Width: 2-7/8" Length: 2-7/8" Height: 0-13/16"



# One-Light Pendant W/HAL AC LED Module

Ceiling cord mounted • Dry location listed PROGRESS LED





## P5340-3030K9

## **Dimming Notes:**

P5340 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## **Dimming Controls**

Lutron Nova T NTELV-300

Lutron Vierti VTELV-600

Lutron Ariadni AYCL-153P

Lutron Diva DVCL-153P

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.