

One-Light Outdoor

Project:

Fixture Type: Location:

Contact:

Wall mounted • Wet location listed PROGRESS LED



P5862-3130K9

Images:

Westport LED offers traditional styling to complement a variety of home decor options. A durable die-cast aluminum frame cradles a softly diffused seeded glass shade. 3000K, 90+ CRI 623 lumens (source). One-light LED wall mount.

Specifications:

Description:

- Black (-31) (powder coat paint)
- Die-cast aluminum Construction •
- Etched Seeded glass shade .
- . LED Module is replaceable (part # 93054049)
- Traditional styling.
- Softly diffused seeded glass shade. .
- . Complements many home decor styles with beaded detailing.
- · 623 lumens 69.2 lumens/watt (source)
- 3000K color temperature, 90+ CRI.
- · Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box •
- Mounting strap for outlet box included
- . 6" of wire supplied
- . ENERGY STAR[®] qualified
- · Meets California Title 24 high efficacy requirements for outdoor use only

Performance:

		Dimen
Number of Modules	1	Width: 6 Depth: 8 Height: H/CTR:
Input Power	9w	
Input Voltage	120 V	
Input Frequency	60 Hz	
Lumens/LPW (Source)	623/69.2 (LM-82)	
Lumens/LPW (Delivered)	322/42.3684210526316 (LM-79)	Glass Width: 5 Length: Height:
ССТ	3000 K	
CRI	90 CRI	
Life (hours)	60,000 (L70/TM-21)	
FCC	Meets FCC Title 47, Part 15 Class B	
Min. Start Temp	-30 °C	
Max. Operating Temp	30 ℃	
Warranty	5 year warranty	
Labels	cCSAus Wet location listed	
	ENERGY STAR [®] qualified	
	Meets California Title 24 high efficacy requirements	
	for outdoor use only	



Dimensions:

6-7/8" 8-3/8" t: 10-1/4" R: 3-1/8"

5" n: 5" t: 4-1/4"



One-Light Outdoor

Wall mounted • Wet location listed PROGRESS LED



P5862-3130K9

Dimming Notes:

P5862 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Nova T NTELV-300

Lutron Vierti VTELV-600

Lutron Ariadni AYCL-153P

Lutron Diva DVCL-153P

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.