

Project:

Fixture Type:

Location:

Contact:

Images:

Post Lantern

Post top - fitter for 3" post or pedestal mounted • Wet location listed PROGRESS LED

Description:

P6430-3130K9

The East Haven LED Collection offers modern styling to complement a wide variety of home styles. The one-light LED post lantern has a Black frame that cradles a seeded glass shade. Fits 3" post (order separately). 120V AC replaceable LED module, 623 lumens (source), 3000K color temperature and 90+ CRI.

Specifications:

- Black (-31) (powder coat paint) •
- Aluminum Construction .
- · Clear Seeded glass shade, White acrylic Diffuser
- LED Module is replaceable (part # 93054049)
- · Contemporary styling.
- · Features clear seeded glass.
- Powder coated finish.
- 623 lumens 69.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI. •
- Dimmable to 10% brightness (See Dimming Notes) •
- Mounting No for outlet box included
- 6" of wire supplied
- ENERGY STAR[®] qualified
- · Meets California Title 24 high efficacy requirements for outdoor use only

Performance:

Number of Modules	1	Diameter: Height: 15'
Input Power	9w	
Input Voltage	120 V	
Input Frequency	60 Hz	Glass Width: 6-1, Length: 6-1 Height: 6-1 Glass 2 Width: 2-7, Length: 2-7 Height: 0-1
Lumens/LPW (Source)	623/69.2 (LM-82)	
Lumens/LPW (Delivered)	196/28 (LM-79)	
CCT	3000 K	
CRI	90 CRI	
Life (hours)	60,000 (L70/TM-21)	
FCC	Meets FCC Title 47, Part 15 Class B	
Min. Start Temp	-30 °C	
Max. Operating Temp	30 °C	
Warranty	5 year warranty	
Labels	cCSAus Wet location listed	
	ENERGY STAR [®] qualified	
	Meets California Title 24 high efficacy requirements	
	for outdoor use only	



Dimensions:

7-1/2"

1/8" 5-1/8" -1/2" 7/8" -7/8" -13/16"



Post Lantern

Post top - fitter for 3" post or pedestal mounted • Wet location listed PROGRESS LED



P6430-3130K9

Dimming Notes:

P6430 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Nova T NTELV-300

Lutron Vierti VTELV-600

Lutron Ariadni AYCL-153P

Lutron Diva DVCL-153P

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.