

Description:

The Leawood LED Collection small wall lantern provides delicate scrollwork with dramatic shadow patterns in a modern form. Intricate die cast aluminum construction in classic White finish. A taller design accommodates the larger scale commonly seen in today's modern and traditional architecture.

Specifications:

- White (-030) (painted)
- Die-cast aluminum Construction
- LED Module is replaceable (part # 93074037)
- Intricate die cast aluminum construction
- Delicate scrollwork with dramatic patterns in a taller design
- The medium wall lantern can be hung on either side of a front or rear door, by a garage, on exterior walls or in porches or outdoor living areas
- LED module hidden inside fixture so no visible light source seen
- Leawood's design and construction is a good fit for Traditional, Mediterranean and transitional homes
- Crisp White finish
- Measures 8in diameter x 13-5/8in ht.
- 9w LED module, 624 lumens 66 lumens/watt (source), 3000K color temperature, 90+ CRI.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box
- Mounting swivel mounting strap for outlet box included
- 6" of wire supplied
- ENERGY STAR® qualified
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	9w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	624/66 (LM-82)
Lumens/LPW (Delivered)	409/43.9 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30°C
Warranty	5 year limited warranty
Labels	cCSAus Wet location listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016

P560104-030-30

Images:



Dimensions:

Diameter: 8"
 Depth: 9-1/2"
 Height: 13-5/8"
 H/CTR: 4-5/8"

P560104-030-30

Dimming Notes:

P560104 is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron - Caseta Wireless

Leviton – 6672

Leviton – 6674

Lutron - AYCL-153P

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton - AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.