

Project:

Fixture Type:

Location:

LED Shaded Sconce

Wall Mounted · Damp Location Listed PROGRESS LED

Contact:



Description:

This wall sconce is ideal for corridor and hotel lighting. Square forms created a stunning brushed bronze frame. The light fixture is topped by a summer linen shade that creates a calming glow sure to welcome tired travelers.

Specifications:

- · Summer Linen fabric Shade
- · This wall sconce is ideal for corridor and hotel lighting.
- · Square forms created a stunning brushed bronze frame.
- The light fixture is topped by a summer linen shade that creates a calming glow sure to welcome tired travelers.
- · Ideal for any hallway, foyer, living room, sitting room, or bedroom.
- Perfect for mid-century modern, transitional, modern, or contemporary settings.
- · Measures 14-inch width by 21-1/4-inch height.
- · Uses one LED module (9w max).
- · Compatible with many Triac/ELV dimmers (see dimming controls)
- Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- · Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 8 in W., 6.5 in ht., 0.812 in depth
- · Mounting plate for outlet box included
- · 6 in of wire supplied
- · Americans With Disabilities Act (ADA) compliant

Performance:

Number of Modules	1
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	624/66 (LM-82)
ССТ	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016

P710054-109-30



Dimensions:

Width: 14 in Height: 21-1/4 in Depth: 3-7/8 in H/CTR: 3-1/4 in

Summer Linen fabric Shade

Width: 16-7/8 in Height: 7-5/16 in



LED Shaded Sconce

Wall Mounted • Damp Location Listed PROGRESS LED



Dimming Notes:

P710054-109-30 is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron Diva DVELV-300P

Lutron Nova T NTELV-300

Lutron Caseta

Lutron Ariadni AY-600P

Leviton Illumatech IPI06-1LZ

Leviton SureSlide 6672

Lutron Ariadni AYCL-153P

Lutron Skylark Contour CTCL-153P

Lutron Diva DVCL-153P

Lutron Toggler TGCL-153P

Lutron Maestro MACL-153M

Lutron Ariadni AYLV-600P

Lutron NOVA T NTLV-600

lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Lutron Renoir II AWRMG-EAW

Lutron Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P710054-109-30