

# LED Etched Glass Sconce

Wall Mounted • Damp Location Listed **PROGRESS LED** 

## Description:

Invite the luxurious demeanor of this angelic wall sconce to illuminate your home with a divine ambiance. A dainty, etched glass shade is crafted in an elongated cup-like shape. The shade is held in place by a beautiful brushed nickel frame sure to look stunning in your home decor design.

## Specifications:

- Etched glass Shade
- Invite the luxurious demeanor of this angelic wall sconce to illuminate your home with a divine ambiance.
- A dainty, etched glass shade is crafted in an elongated cup-like shape.
- The shade is held in place by a beautiful brushed nickel frame sure to look stunning in your home decor design.
- Ideal for any bathroom, hallway, foyer, or stairway.
- Perfect for transitional, modern, or contemporary settings.
- Measures 6-inch width by 11-inch height.
- Uses one LED module (9w max).
- Compatible with many Triac/ELV dimmers (see dimming controls)
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 6 in W., 9.87 in ht., 0.312 in depth
- Mounting plate for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

## Performance:

Number of Modules	1
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	624/66 (LM-82)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016


# P710079-009-30



## Dimensions:

Width: 6 in  
 Height: 11 in  
 Depth: 4 in  
 H/CTR: 3-1/2 in

Etched glass Shade  
 Width: 5-3/4 in  
 Height: 10-5/16 in



**Dimming Notes:**

---

P710079-009-30 is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

**Dimming Controls:**

---

Lutron Diva DVELV-300P

Lutron Nova T NTELV-300

Lutron Caseta

Lutron Ariadni AY-600P

Leviton Illumatech IPI06-1LZ

Leviton SureSlide 6672

Lutron Ariadni AYCL-153P

Lutron Skylark Contour CTCL-153P

Lutron Diva DVCL-153P

Lutron Toggler TGCL-153P

Lutron Maestro MACL-153M

Lutron Ariadni AYLV-600P

Lutron NOVA T NTLV-600

lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Lutron Renoir II AWRMG-EAW

Lutron Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

# P710079-009-30