



# 1 in. Liquidtight Straight Connector, Insulated with Ground Lug

By Raco  
Catalog # 3514-3

1 in. Liquidtight Straight Connector, Insulated with Ground Lug



\*Representative Image

## Features

- Steel construction ensures mechanical protection
- All metallic components are zinc electroplated for added corrosion protection
- Insulated with ground lug
- Patented split gland-ring assures a perfect seal, preventing pullouts
- UL Listed, CSA
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

## General

|                          |                      |
|--------------------------|----------------------|
| Catalog Number           | 3514-3               |
| Conduit Type             | Liquidtight          |
| Connector Type           | Grounding            |
| EU RoHS Indicator        | Yes                  |
| Environmental Conditions | Wet Location         |
| Fitting Type             | Connectors           |
| Insulation Type          | Insulated            |
| Material                 | Steel/Malleable Iron |
| UPC                      | 050169351437         |

## Dimensions

|            |                                |
|------------|--------------------------------|
| Dimensions | 1.797 in x 1.703 in x 1.703 in |
| Height     | 1.703 in                       |
| Length     | 1.797 in                       |
| Trade Size | 1 in                           |
| Weight     | 0.426 lb                       |

Width 1.703 in

## Electrical Ratings

|                                    |         |
|------------------------------------|---------|
| Grounding Wire Capacity<br>Maximum | #4 STR  |
| Grounding Wire Capacity<br>Minimum | #14 SOL |

## Certifications And Compliance

|  |   |
|--|---|
| Buy American Compliant<br>Certified Listed | Contact Manufacturer <ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>  |
| Hazardous Rating(s)                        | <ul style="list-style-type: none"><li>• Class I, Division 2</li><li>• Class II Division 1 &amp; 2</li><li>• Class III, Division 1 &amp; 2</li></ul> |
| Industry Standard(s)                       | UL 514B   |

## Logistics

|                       |    |
|-----------------------|----|
| Carton Quantity       | 10 |
| Minimum Pack Quantity | 10 |

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC-E195975-4](#)  
[Product Logo - LT COND](#)  
[Sales Drawings - 35143 Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)